

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® RWV-M	52107850 14.11.2013

Strain relief
Sealed by incised sealing ring
Corrosion-resistant
Decrease in installation height
Seawater-resistant



Corrosion-resistant



Space requirement



Connector with standard housing unit



Temperature-resistant

Application range

Angled glands are used in areas where cables have to run in parallel to the housing wall.
Electric motor manufacturing
Machine and equipment manufacturing
Plant engineering
Light and sound applications

Design

Metric connection thread acc. to EN 50262

Note

Counter nut to be used: SKINDICHT® SM-M

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® RWV-M	1 / 3
--------------------	----------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® RWV-M	52107850 14.11.2013

Technical Data

Article designation / size:	40 x 1,5
Clamping range ØF (mm):	32 - 23
L:	43
SW1:	42
Ø A1:	45
SW2:	40
Ø A2:	43.5
Ø G:	35
Height (mm):	5
Overall length, C (mm):	53,1
Thread length, D (mm):	15.5
SW3:	46
Pieces / PU:	5
Material:	Body: zinc die-casting, nickel-plated Compression screw and hexagon nut: nickel-plated brass Incised sealing ring: CR/NBR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +100°C

Product Management	Document: SKINDICHT® RWV-M	2 / 3
--------------------	----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINDICHT® RWV-M	52107850 14.11.2013



Product Management	Document: SKINDICHT® RWV-M	3 / 3
--------------------	----------------------------	-------