

### 1.0X0.5mm SMD CHIP LED LAMP

Part Number: KPHHS-1005CGCK

Green


### **Features**


- 1.0mmX0.5mm SMT LED, 0.5mm thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel .
- Moisture sensitivity level : level 3.
- RoHS compliant.


## Description

The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode.


# **Package Dimensions**











- All dimensions are in millimeters (inches).
   Tolerance is ±0.1(0.004") unless otherwise noted.
- 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

  4. The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAC5628 **REV NO: V.16B DATE: FEB/27/2013** PAGE: 1 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: F.Cui ERP: 1203002672

## **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
		2.	Min.	Тур.	201/2
KPHHS-1005CGCK	Green (AlGaInP)	Water Clear	20	50	120°

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
  2. Luminous intensity/ luminous Flux: +/-15%.
- 3. Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

# Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	574		nm	IF=20mA
λD [1]	Dominant Wavelength	Green	570		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	20		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Green	2.1	2.5	V	IF=20mA
lr	Reverse Current	Green		10	uA	VR=5V

## Notes:


- 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

# Absolute Maximum Ratings at TA=25°C

Parameter	Green	Units		
Power dissipation	75	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	150	mA		
Reverse Voltage	5	V		
Operating Temperature	-40°C To +85°C			
Storage Temperature	-40°C To +85°C			

1. 1/10 Duty Cycle, 0.1ms Pulse Width.

SPEC NO: DSAC5628 **REV NO: V.16B DATE: FEB/27/2013** PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: F.Cui ERP: 1203002672



 SPEC NO: DSAC5628
 REV NO: V.16B
 DATE: FEB/27/2013
 PAGE: 3 OF 5


 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: F.Cui
 ERP: 1203002672

SPATIAL DISTRIBUTION

### KPHHS-1005CGCK

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

  3.Number of reflow process shall be 2 times or less.


# **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



**Reel Dimension** 




## **Tape Dimensions** (Units : mm)





SPEC NO: DSAC5628 **REV NO: V.16B DATE: FEB/27/2013** PAGE: 4 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: F.Cui ERP: 1203002672

# **PACKING & LABEL SPECIFICATIONS**

### KPHHS-1005CGCK







Detailed application notes are listed on our website. http://www.kingbright.com/application\_notes

SPEC NO: DSAC5628 APPROVED: WYNEC REV NO: V.16B CHECKED: Allen Liu DATE: FEB/27/2013 DRAWN: F.Cui PAGE: 5 OF 5 ERP: 1203002672