

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SHV-M-VITON®</b>	52105470 14.11.2013

For high temperatures  
Resistant to oils, solvents, acids and chemicals  
Watertight  
High strain relief  
Robust



Robust



Temperature-resistant



Waterproof



#### Application range

Watertight and high temperature-resistant cable gland with special conical VITON® sealing element.

Brickworks

Sewage treatment plants

Car wash sites

#### Design

1 fitting

2 washers

3 VITON® sealing cone

4 brass cones

5 compression screws

#### Note

Counter nut to be used: SKINDICHT® SM-M

Example description: SHV-M-Viton® 20/11/720 = metric connection thread11 = PG function thread7 = clear opening of sealing cone

#### Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SHV-M-VITON®	1 / 3
--------------------	-----------------------------------	-------



U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SHV-M-VITON®</b>	<b>52105470</b> <b>14.11.2013</b>

### Technical Data

Article designation / size:	20 x 1,5
Clamping range ØF (mm):	6,8 - 8,8
Function thread PG:	11
SW (mm):	22 / 20
Overall length, C (mm):	31
Thread length, D (mm):	6
Clear opening F (mm):	9
Pieces / PU:	25
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Sealing cone: FKM O-ring: FKM
Protection rating:	IP 68 - 10 bar
Temperature range:	-15°C to +200°C

Product Management	Document: SKINDICHT® SHV-M-VITON®	2 / 3
--------------------	-----------------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	<b>SKINDICHT® SHV-M-VITON®</b>	52105470 14.11.2013



Product Management	Document: SKINDICHT® SHV-M-VITON®	3 / 3
--------------------	-----------------------------------	-------