2.0x1.25mm SMD CHIP LED LAMP

Super Bright Orange Part Number: KP-2012SECK


Features

- 2.0mmx1.25mm SMT LED,1.1mm thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package : 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

Description

The Super Bright Orange device is made with AlGaInP (on GaAs substrate) light emitting diode chip.

Package Dimensions



SPEC NO: DSAB3510 **APPROVED: WYNEC**

Notes:

REV NO: V.15A **CHECKED:** Allen Liu

DATE: DEC/29/2011 **DRAWN: C.H.Han**

PAGE: 1 OF 5 ERP: 1203000163

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KP-2012SECK	Super Bright Orange (AlGaInP)	Water Clear	120	250	120°
		Waler Ciedi	*80	*180	

Notes:

1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

Luminous intensity/ luminous Flux: +/-15%.
* Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Orange	610		nm	I⊧=20mA
λD [1]	Dominant Wavelength	Super Bright Orange	601		nm	I⊧=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Orange	29		nm	I⊧=20mA
С	Capacitance	Super Bright Orange	15		pF	VF=0V;f=1MHz
Vf [2]	Forward Voltage	Super Bright Orange	2.1	2.5	V	I⊧=20mA
lr	Reverse Current	Super Bright Orange		10	uA	VR=5V

Notes:

1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.


3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C

Parameter	Super Bright Orange	Units		
Power dissipation	75	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	195	mA		
Reverse Voltage	5	V		
Operating Temperature	-40°C To +85°C			
Storage Temperature	-40°C To +85°C			


Note:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.



KP-2012SECK

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.



SPEC NO: DSAB3510 APPROVED: WYNEC

CHECKED: Allen Liu

DATE: DEC/29/2011 DRAWN: C.H.Han PAGE: 4 OF 5 ERP: 1203000163

