

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SKZ</b>	52004290 14.11.2013

With incised sealing ring for adjustment to several cable diameters  
High strain relief  
High mechanical stability



Wide clamping range



Optimum strain relief



Robust



### Application range

Saddle clamp strain relief gland for harsh application conditions.  
Building sites  
Plant engineering  
Electric motor manufacturing

### Design

PG connection thread

### Note

SKINDICHT® SKZ-XL is similar to the SKINDICHT® SKZ, but has an extended connection thread for thick walls  
Counter nut to be used: SKINDICHT® SM  
Refer to SKINDICHT® EV for additional accessories

### Remark


Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article designation / size:	SKZ 11
Clamping range ØF (mm):	8 - 12
Max. fitting size for installation (mm):	27
SW1/SW2 mm:	20 / 21
Overall length, C (mm):	30
Thread length, D (mm):	6
Pieces / PU:	50
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Incised sealing ring: CR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +80°C

Product Management	Document: SKINDICHT® SKZ	1 / 2
--------------------	--------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SKZ</b>	52004290 14.11.2013



Product Management	Document: SKINDICHT® SKZ	2 / 2
--------------------	--------------------------	-------