


U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SKZ-M	52106800 14.11.2013

With incised sealing ring for adjustment to several cable diameters
High strain relief
High mechanical stability



Mechanical resistance



Optimum strain relief

Application range

Saddle clamp strain relief gland for harsh application conditions.
Building sites
Plant engineering
Electric motor manufacturing

Design

Metric connection thread acc. to EN 50262

Note

SKINDICHT® SHZ-M-XL is similar to the SKINDICHT® SHZ-M, but has an extended connection thread for thick walls
Counter nut to be used: SKINDICHT® SM-M
Example description: SKZ-M 16/916 = connection thread 9 = PG function thread

Remark

Photographs are not to scale and do not represent detailed images of the respective products.


Technical Data

Article designation / size:	16 x 1,5
Ø-F mm:	5 - 8
Max. fitting size for installation (mm):	24
Function thread PG:	9
SW1/SW2 mm:	18 / 17
Overall length, C (mm):	29
Thread length, D (mm):	5
Pieces / PU:	50
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Incised sealing ring: CR/NBR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +80°C



Product Management	Document: SKINDICHT® SKZ-M	1 / 2
--------------------	----------------------------	-------

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SKZ-M	52106800 14.11.2013



Product Management	Document: SKINDICHT® SKZ-M	2 / 2
--------------------	----------------------------	-------