3.2x1.6mm SMD CHIP LED LAMP

Part Number: KPTD-3216SURCK Hyper Red

Features

- 3.2mmX1.6mm SMT LED, 1.8mm thickness.
- Low power consumption.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel .
- Moisture sensitivity level : level 3.
- RoHS compliant.

Description

The Hyper Red source color devices are made with Al-GalnP on GaAs substrate Light Emitting Diode.

Package Dimensions



SPEC NO: DSAA4410 APPROVED: WYNEC REV NO: V.19A CHECKED: Allen Liu DATE: FEB/20/2013 DRAWN: Q.M.Chen PAGE: 1 OF 5 ERP: 1203002303

Soloction Guido

Selection Guide									
Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]				
				Тур.	201/2				
KPTD-3216SURCK	Hyper Red (AlGaInP)	Water Clear	700	1500	35°				
			*300	*800					

Notes:

1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
Luminous intensity/ luminous Flux: +/-15%.
* Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Hyper Red	645		nm	I⊧=20mA
λD [1]	Dominant Wavelength	Hyper Red	630		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Hyper Red	28		nm	I⊧=20mA
С	Capacitance	Hyper Red	35		pF	VF=0V;f=1MHz
Vf [2]	Forward Voltage	Hyper Red	1.95	2.5	V	I⊧=20mA
lr	Reverse Current	Hyper Red		10	uA	VR=5V

Notes: 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.

3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C

Parameter	Hyper Red	Units	
Power dissipation	75	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	185	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		

Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.



KPTD-3216SURCK

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.



DATE: FEB/20/2013 DRAWN: Q.M.Chen

