Reliable bending and anti-kink protection
High strain relief
Robust
For cables with large outer diameters
High degree of protection



Wide clamping range

Optimum strain relief

Robust

Application range

Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0700-1
Handheld device
Portable equipment
Building sites
Moving machine parts

Design

PG connection thread

Note

Counter nut to be used: SKINDICHT® SM
For EMC version, refer to SKINDICHT® SRE

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	SR 21/20
Clamping range ØF (mm):	18 - 20
Max. fitting size for installation (mm):	46
SW1/SW2 mm:	30 / 30
Overall length, C (mm):	79
Thread length, D (mm):	7
Pieces / PU:	25
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass O-ring: NBR Anti-kink protection: CR
Protection rating:	IP 65
Temperature range:	-20°C to +80°C

PN 0486/01_03.10
©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.