

3.2x2.4mm SMD CHIP LED LAMP

Part Number: KPBD-3224ESGC

High Efficiency Red Super Bright Green

Features


- 3.2x2.4mm SMT LED, 2.4mm thickness.
- Low power consumption.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 1500pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.1(0.004") unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
 The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAC2535 **REV NO: V.13A DATE: MAR/28/2013** PAGE: 1 OF 6 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203000867

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KPBD-3224ESGC	High Efficiency Red (GaAsP/GaP)	Water Clear	30	70	20°
			*12	*40	
	Super Bright Green (GaP)		20	55	
			*20	*55	

- Notes:
 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 2. Luminous intensity/ luminous Flux: +/-15%.
 *Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red Super Bright Green	627 565		nm	IF=20mA
λD [1]	Dominant Wavelength	High Efficiency Red Super Bright Green	617 568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red Super Bright Green	45 30		nm	IF=20mA
С	Capacitance	High Efficiency Red Super Bright Green	15 15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	High Efficiency Red Super Bright Green	2 2.2	2.5 2.5	V	IF=20mA
lR	Reverse Current	High Efficiency Red Super Bright Green		10 10	uA	VR = 5V

Notes:

- 1.Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.


 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C


Parameter	High Efficiency Red	Super Bright Green	Units		
Power dissipation	75	62.5	mW		
DC Forward Current	30	25	mA		
Peak Forward Current [1]	160	140	mA		
Reverse Voltage		V			
Operating Temperature	-40°C To +85°C				
Storage Temperature	-40°C To +85°C				


1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAC2535 **REV NO: V.13A DATE: MAR/28/2013** PAGE: 2 OF 6 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203000867





KPBD-3224ESGC High Efficiency Red














 SPEC NO: DSAC2535
 REV NO: V.13A
 DATE: MAR/28/2013
 PAGE: 3 OF 6


 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1203000867


Super Bright Green











SPATIAL DISTRIBUTION


 SPEC NO: DSAC2535
 REV NO: V.13A
 DATE: MAR/28/2013
 PAGE: 4 OF 6

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1203000867

KPBD-3224ESGC

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

 1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.

 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.


 3.Number of reflow process shall be 2 times or less.


Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)



Tape Dimensions (Units: mm)

Reel Dimension








SPEC NO: DSAC2535 **REV NO: V.13A DATE: MAR/28/2013** PAGE: 5 OF 6 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203000867

PACKING & LABEL SPECIFICATIONS

KPBD-3224ESGC







Detailed application notes are listed on our website. http://www.kingbright.com/application notes

SPEC NO: DSAC2535 APPROVED: WYNEC REV NO: V.13A CHECKED: Allen Liu DATE: MAR/28/2013 DRAWN: Y.Liu PAGE: 6 OF 6 ERP: 1203000867