

### 3.2x2.4mm SMD CHIP LED LAMP

Part Number: KPBD-3224SURKCGKC

Hyper Red Green

#### **Features**


- 3.2x2.4mm SMT LED, 2.4mm thickness.
- Low power consumption.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 1500pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.


### Description


The Hyper Red source color devices are made with Al-GaInP on GaAs substrate Light Emitting Diode.

The Green source color devices are made with AlGalnP on GaAs substrate Light Emitting Diode.

# **Package Dimensions**







- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is  $\pm 0.1(0.004")$  unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
   The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAD3553 **REV NO: V.14A** DATE: MAR/28/2013 PAGE: 1 OF 6 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203000875

### **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
		-	Min.	Тур.	201/2
KPBD-3224SURKCGKC	Hyper Red (AlGaInP)	Water Clear	700	1300	- 20°
			*120	*400	
	Green (AlGalnP)		80	280	
			*80	*280	

- Notes:
  1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
  2. Luminous intensity/ luminous Flux: +/-15%.

  \* Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

## Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Hyper Red Green	645 574		nm	IF=20mA
λD [1]	Dominant Wavelength	Hyper Red Green	630 570		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Hyper Red Green	28 20		nm	IF=20mA
С	Capacitance	Hyper Red Green	35 15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Hyper Red Green	1.95 2.1	2.5 2.5	V	IF=20mA
lr	Reverse Current	Hyper Red Green		10 10	uA	VR = 5V

### Notes:


- 1.Wavelength: +/-1nm.
- Forward Voltage: +/-0.1V.
   Wavelength value is traceable to the CIE127-2007 compliant national standards.

# Absolute Maximum Ratings at TA=25°C


Parameter	Hyper Red	Green	Units		
Power dissipation	75	75	mW		
DC Forward Current	30	30	mA		
Peak Forward Current [1]	185	150	mA		
Reverse Voltage		V			
Operating Temperature	-40°C To +85°C				
Storage Temperature	-40°C To +85°C				


Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAD3553 **REV NO: V.14A** DATE: MAR/28/2013 PAGE: 2 OF 6 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203000875





# KPBD-3224SURKCGKC Hyper Red














 SPEC NO: DSAD3553
 REV NO: V.14A
 DATE: MAR/28/2013
 PAGE: 3 OF 6


 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1203000875


## Green












Ambient Temperature T<sub>A</sub> (°C) LUMINOUS INTENSITY Vs. AMBIENT TEMPERATURE



SPATIAL DISTRIBUTION

 SPEC NO: DSAD3553
 REV NO: V.14A
 DATE: MAR/28/2013
 PAGE: 4 OF 6

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1203000875

#### **KPBD-3224SURKCGKC**

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.

  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.


  3.Number of reflow process shall be 2 times or less.


# **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



# **Tape Dimensions** (Units: mm)

### **Reel Dimension**








SPEC NO: DSAD3553 **REV NO: V.14A DATE: MAR/28/2013** PAGE: 5 OF 6 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203000875

### **PACKING & LABEL SPECIFICATIONS**

### KPBD-3224SURKCGKC







Detailed application notes are listed on our website. <a href="http://www.kingbright.com/application">http://www.kingbright.com/application</a> notes

SPEC NO: DSAD3553 APPROVED: WYNEC REV NO: V.14A CHECKED: Allen Liu DATE: MAR/28/2013 DRAWN: Y.Liu PAGE: 6 OF 6 ERP: 1203000875