

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SR-SV	52023623 14.11.2013

For high temperatures
Resistant to oils, solvents, acids and chemicals
Seawater-resistant
High strain relief
Robust



Good chemical resistance



Optimum strain relief



Robust



Temperature-resistant

Application range

Special cable gland with VITON® anti-kink sleeve. Our own reinforced acid-resistant VITON® receptacle does not show any effects of aging even after an extended period of use at a temperature of +165°C.

Machine and turbine manufacturing
Power plant engineering
Laboratory

Design

PG connection thread

Note

Counter nut to be used: SKINDICHT® SM
EMC version is available upon request

Remark

Viton® is a registered trademark of DuPont de Nemours
Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SR-SV	1 / 3
--------------------	----------------------------	-------


U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SR-SV	52023623 14.11.2013

Technical Data

Article designation / size:	SR-SV 13/11
Clamping range ØF (mm):	9 - 11
Max. fitting size for installation (mm):	32
SW1/SW2 mm:	22 / 22
Overall length, C (mm):	62
Thread length, D (mm):	6.5
Pieces / PU:	25
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass O-ring: FKM Anti-kink protection: FKM
Protection rating:	IP 65
Temperature range:	-15°C to +165°C

Product Management	Document: SKINDICHT® SR-SV	2 / 3
--------------------	----------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	SKINDICHT® SR-SV	52023623 14.11.2013



Product Management	Document: SKINDICHT® SR-SV	3 / 3
--------------------	----------------------------	-------