

9.9mm (0.39INCH) SINGLE DIGIT NUMERIC DISPLAY

Part Number: SC39-11SYKWA

Super Bright Yellow


Features

- 0.39 inch digit height.
- Low current operation.
- Excellent character appearance.
- Easy mounting on P.C. boards or sockets.
- Mechanically rugged.
- Standard : gray face, white segment.
- RoHS compliant.

Description

The Super Bright Yellow device is made with AlGaInP (on GaAs substrate) light emitting diode chip.

Package Dimensions& Internal Circuit Diagram



Notes



2. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

SPEC NO: DSAH3991 REV NO: V.6A DATE: MAY/10/2013
APPROVED: WYNEC CHECKED: Joe Lee DRAWN: Q.M.CHEN



DATE: MAY/10/2013 PAGE: 1 OF 6
DRAWN: Q.M.CHEN ERP: 1301002297

Selection Guide

| Part No. | Dice | Lens Type | Iv (ucd) [1] @ 10mA | | Description |
|--------------|-------------------------------|----------------|------------------------|--------|-------------------------------------|
| | | | Min. | Тур. | |
| SC39-11SYKWA | Super Bright Yellow (AlGaInP) | White Diffused | 31000 | 86000 | Common Cathode, Rt.Hand Decimal. |
| | | | *14000 | *26000 | |

- Note:
 1. Luminous intensity/ luminous Flux: +/-15%.

 * Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

| Symbol | Parameter | Device | Тур. | Max. | Units | Test Conditions |
|--------|--------------------------|---------------------|------|------|-------|--------------------|
| λpeak | Peak Wavelength | Super Bright Yellow | 590 | | nm | IF=20mA |
| λD [1] | Dominant Wavelength | Super Bright Yellow | 590 | | nm | IF=20mA |
| Δλ1/2 | Spectral Line Half-width | Super Bright Yellow | 20 | | nm | IF=20mA |
| С | Capacitance | Super Bright Yellow | 20 | | pF | VF=0V;f=1MHz |
| VF [2] | Forward Voltage | Super Bright Yellow | 2.0 | 2.5 | V | I=20mA |
| lr | Reverse Current | Super Bright Yellow | | 10 | uA | V _R =5V |


- Notes:
 1.Wavelength: +/-1nm.
 2. Forward Voltage: +/-0.1V.
 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C

| Parameter | Super Bright Yellow | Units | | |
|---------------------------------|--------------------------------------|-------|--|--|
| Power dissipation | 75 | mW | | |
| DC Forward Current | 30 | mA | | |
| Peak Forward Current [1] | 175 | mA | | |
| Reverse Voltage | 5 | V | | |
| Operating / Storage Temperature | -40°C To +85°C | | | |
| Lead Solder Temperature[2] | Temperature[2] 260°C For 3-5 Seconds | | | |


- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
 2. 2mm below package base.


SPEC NO: DSAH3991 **REV NO: V.6A** DATE: MAY/10/2013 PAGE: 2 OF 6 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: Q.M.CHEN ERP: 1301002297





Super Bright Yellow

SC39-11SYKWA










SPEC NO: DSAH3991 APPROVED: WYNEC REV NO: V.6A CHECKED: Joe Lee DATE: MAY/10/2013 DRAWN: Q.M.CHEN PAGE: 3 OF 6 ERP: 1301002297




SPEC NO: DSAH3991 APPROVED: WYNEC REV NO: V.6A CHECKED: Joe Lee DATE: MAY/10/2013 DRAWN: Q.M.CHEN PAGE: 4 OF 6 ERP: 1301002297

THROUGH HOLE DISPLAY MOUNTING METHOD


Lead Forming


Do not bend the component leads by hand without proper tools. The leads should be bent by clinching the upper part of the lead firmly such that the bending force is not exerted on the plastic body.



Installation

- 1. The installation process should not apply stress to the lead terminals.
- 2. When inserting for assembly, ensure the terminal pitch matches the substrate board's hole pitch to prevent spreading or pinching the lead terminals.





3. The component shall be placed at least 5mm from edge of PCB to avoid damage caused excessive heat during wave soldering.






SPEC NO: DSAH3991 APPROVED: WYNEC REV NO: V.6A CHECKED: Joe Lee DATE: MAY/10/2013 DRAWN: Q.M.CHEN PAGE: 5 OF 6 ERP: 1301002297

DISPLAY SOLDERING CONDITIONS

Wave Soldering Profile For Lead-free Through-hole LED.



NOTES:

- 1.Recommend the wave temperature 245°C~260°C.The maximum soldering temperature should be less than 260°C.
- 2.Do not apply stress on epoxy resins when temperature is over 85°C.
- 3. The soldering profile apply to the lead free soldering (Sn/Cu/Ag alloy).
- 4. During wave soldering , the PCB top-surface temperature should be kept below 105 °C
- 5.No more than once.

Soldering General Notes:


- 1. Through—hole displays are incompatible with reflow soldering.
- 2. If components will undergo multiple soldering processes, or other processes where the components may be subjected to intense heat, please check with Kingbright for compatibility.

CLEANING

- 1.Mild "no-clean" fluxes are recommended for use in soldering.
- If cleaning is required, Kingbright recommends to wash components with water only. Do not use harsh organic solvents for cleaning, because they may damage the plastic parts .And the devices should not be washed for more than one minute.

CIRCUIT DESIGN NOTES

- 1.Protective current-limiting resistors may be necessary to operate the Displays.
- 2.LEDs mounted in parallel should each be placed in series with its own current—limiting resistor.



Detailed application notes are listed on our website. http://www.kingbright.com/application notes

SPEC NO: DSAH3991 REV NO: V.6A DATE: MAY/10/2013 PAGE: 6 OF 6

APPROVED: WYNEC CHECKED: Joe Lee DRAWN: Q.M.CHEN ERP: 1301002297