

# ROYALOHM

*C O N F I D E N T I A L D O C U M E N T*

SPECIFICATION FOR APPROVAL

**CONRAD**

Description : (CFR) Coated Type Kit Resistors  
100pcs./polybag kit

Royalohm Part no.:  
CFR0W4JxxxxKIT

Approved by

**Parts corresponding to RoHS Compliant: 2005-Apr.-1**

Royal Electronic Factory (Thailand) Co., Ltd.

20/1-2 Moo 2 Klong-Na, Muang

Chachoengsao 24000, Thailand

Tel: +66-38-822404-8

Fax: +66 38-981190 / 823765

E-mail Address: Export sales: [Export@royalohm.com](mailto:Export@royalohm.com)

Local sales: [Local@royalohm.com](mailto:Local@royalohm.com)

<http://www.royalohm.com>

P.O. Box 251 Klongchan, Bangkok 10240, Thailand

| Approved     | Checked            | Prepared       |
|--------------|--------------------|----------------|
| Mr. Jack Lin | Mr. S. Polthanasan | Ms. P. Supatta |

Issue Date: 2013/12/14

| <b>CHANGE NOTIFICATION HISTORY</b> |                        |                |               |
|------------------------------------|------------------------|----------------|---------------|
| <b>Version</b>                     | <b>Date of Version</b> | <b>History</b> | <b>Remark</b> |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |
|                                    |                        |                |               |

|                         |                                 |
|-------------------------|---------------------------------|
| <b>Customer: CONRAD</b> | <b>Part No.: CFR0W4JxxxxKIT</b> |
|-------------------------|---------------------------------|

1. Scope:

This specification for approval relates to Coated Type Kit Resistors (CFR) manufactured by ROYALOHM 's specifications.

2. Type designation:

The type designation shall be in the following form :

|       |      |              |                         |                       |
|-------|------|--------------|-------------------------|-----------------------|
| (Ex.) | CR   | 1/4W         | J                       | 10Ω                   |
|       | Type | Power Rating | Resistance<br>Tolerance | Nominal<br>Resistance |

3. Ratings:

Ratings shall be shown in the table 1.

Table 1

| Type                            | CR               |
|---------------------------------|------------------|
| Rated Power                     | 0.25 W at 70°C   |
| Max. Working Voltage            | 250 V            |
| Max. Overload Voltage           | 500 V            |
| Dielectric Withstanding Voltage | 500 V            |
| Rated Ambient Temp.             | 70 °C            |
| Operating Temp.Range.           | -55°C --- +155°C |
| Resistance Tolerance            | ± 5 %            |
| Resistance Range                | 1Ω----10MΩ       |

3.1 Power rating:

Resistors shall have a power rating based on continuous full load operation at an ambient temperature of 70 °C. For temperature in excess of 70 °C , the load shall be derated as shown in the figure 1.

3.2 Voltage rating:

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercial-line frequency and waveform corresponding to the power rating , as determined from the following formula :

$$RCWV = \sqrt{P \times R}$$

Were : RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (volt)


P = Power Rating (watt)

R = Nominal Resistance (ohm)

### Coated Type Kit Resistors (CFR)

In no case shall the rated DC or RMS AC continuous working voltage be greater than the applicable maximum value.


Figure 1.



3.3 Nominal resistance :

Effective figures of nominal resistance shall be in accordance with E-24 series, and resistance tolerance shall be shown by table 1.

4. Construction :



| No. | Name            | Material                                |
|-----|-----------------|---|
| 1   | Basic Body      | Rod Type Ceramics                       |
| 2   | Resistance Film | Carbon Film                             |
| 3   | End Cap         | Steel (Tin plated iron surface)         |
| 4   | Lead Wire       | Annealed copper wire coated with tin    |
| 5   | Joint           | By welding                              |
| 6   | Coating         | Insulated epoxy resin ( Color : Beige ) |
| 7   | Color Code      | Epoxy Resin                             |


| <b>Coated Type Kit Resistors (CFR)</b> |  |  |
|--|--|--|
| <b>5. Characteristics :</b>            |  |  |
| Characteristics                        | Limits   | Test Methods<br>( JIS C 5201-1 )   |
| DC. resistance                         | Must be within the specified tolerance.  | The limit of error of measuring apparatus shall not exceed allowable range or 5% of resistance tolerance<br>(Sub-clause 4.5)   |
| Insulation resistance                  | Insulation resistance is 10,000 MΩ Min   | Resistors shall be clamped in the trough of a 90° metallic V-block or foil method use a metal foil shall be wrapped closely around the body of the resistor. After that shall be tested at DC potential respectively specified in the above list for 60 +10/-0 secs.<br>(Sub-clause 4.6)   |
| Dielectric withstanding voltage        | No evidence of flashover mechanical damage, arcing or insulation break down          | Resistors shall be clamped in the trough of a 90° metallic V-block or foil method use a metal foil shall be wrapped closely around the body of the resistor. After that shall be tested at AC potential respectively specified in the table 1. for 60 +10/-0 secs.<br>(Sub-clause 4.7)   |
| Temperature coefficient                | Resis.Range  | Natural resistance change per temp. degree centigrade.<br>$\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \quad (\text{PPM}/^\circ\text{C})$ R1: Resistance value at room temperature (t1)<br>R2: Resistance value at room temp.plus 100°C (t2)<br>(Sub-clause 4.8)  |
|  | T.C.R. (PPM/°C)  |  |
|  | $\leq 10 \Omega$<br>11Ω ~ 99K<br>100K ~ 1M<br>1.1M ~ 10M                             |  |
| Short time overload                    | Resistance change rate is ± (1 % + 0.05Ω) Max. with no evidence of mechanical damage | Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds.<br>(Sub-clause 4.13)   |
| Terminal strength                      | No evidence of mechanical damage.  | <b>Direct load :</b><br>Resistance to a 2.5 kgs direct load for 10 secs. in the direction of the longitudinal axis of the terminal leads.<br><b>Twist test :</b><br>Terminal leads shall be bent through 90 ° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about the original axis of the bent terminal in alternating direction for a total of 3 rotations.<br>(Sub-clause 4.16) |

| Coated Type Kit Resistors (CFR)                   |  |                    |  |
|---|--|--------------------|--|
| Characteristics                                   | Limits   |                    | Test Methods<br>( JIS C 5201-1 )   |
| Solderability                                     | 95 % coverage Min.   |                    | The area covered with a new , smooth clean , shiny and continuous surface free from concentrated pinholes.<br>Test temp. of solder : 245°C ± 3°C<br>Dwell time in solder : 2 ~ 3 seconds<br>(Sub-clause 4.17)  |
| Soldering temp. reference                         | Electrical characteristics shall be satisfied. Without distinct deformation in appearance.<br>(95 % coverage Min.) |                    | The leads immersed into solder bath to 3.2 to 4.8 mm. from the body. Permanent resistance change shall be checked.<br><u>Wave soldering condition: (2 cycles Max.)</u><br>Pre-heat : 100 ~ 120 °C, 30 ± 5 sec.<br>Suggestion solder temp.: 235 ~ 255 °C, 10 sec. (Max.)<br>Peak temp.: 260 °C<br><u>Hand soldering condition:</u><br>Hand Soldering bit temp. : 380 ± 10 °C<br>Dwell time in solder : 3 +1/-0 sec. |
| Resistance to soldering heat                      | Resistance change rate is ± (1% + 0.05 Ω) Max. with no evidence of mechanical damage.                              |                    | Permanent resistance change when leads immersed to 3.2 to 4.8 mm from the body in 350°C ± 10 °C solder for 3 ± 0.5 seconds<br>(Sub-clause 4.18)  |
| Temperature cycling                               | Resistance change rate is ± (1% + 0.05 Ω) Max. with no evidence of mechanical damage.                              |                    | Resistance change after continuous 5 cycles for duty shown below:  |
|   |  |                    | <b>Step</b> <b>Temperature</b> <b>Time</b>   |
|   |  |                    | 1              -55°C ±3°C              30 mins   |
|   |  |                    | 2              Room temp.              10~15 mins  |
|   |  |                    | 3              +155°C ±2°C              30 mins  |
| 4              Room temp.              10~15 mins |  |                    |  |
|   |  |                    | (Sub-clause 4.19)  |
| Vibration   | Resistance change rate is ± (1% + 0.05 Ω) Max.   |                    | 55Hz, 3 planes 2hrs each<br>Total amplitude = 1.5mm<br>(Sub-clause 4.22)   |
| Load life in humidity                             | <b>Resistance value</b> $\Delta R/R$   |                    | Resistance change after 1,000 hours operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") in a humidity test chamber controlled at 40 °C ± 2 °C and 90 to 95 % relative humidity<br>(Sub-clause 4.24.2.1)  |
|   | Normal   | < 100KΩ      ± 3 % |  |
|   | Type   | ≥ 100KΩ      ± 5 % |  |
| Load life   | <b>Resistance value</b> $\Delta R/R$   |                    | Permanent resistance change after 1,000 hours operating at RCWV with duty cycle of ( 1.5 hours "on", 0.5 hour "off" ) at 70°C ± 2°C ambient<br>(Sub-clause 4.25.1)   |
|   | Normal   | < 56KΩ      ± 2 %  |  |
|   | Type   | ≥ 56KΩ      ± 3 %  |  |
| Resistance to solvent                             | No deterioration of protective coatings and markings   |                    | Specimens shall be immersed in a bath of trichroethane completely for 3 minutes with ultrasonic<br>(Sub-clause 4.30)   |

### Coated Type Kit Resistors (CFR)

6. Dimension :


Unit : mm



| Type | Power Rating | D (Max.) | L (Max.) | $d \pm 0.05$ | $H \pm 3$ |
|------|--------------|----------|----------|--------------|-----------|
| CR   | 1/4W         | 2.5 mm   | 6.8 mm   | 0.54 mm      | 28 mm     |

Painting method:


Welding point, terminal and lead wire, is permissible to be exposed without the outer coated cover. The extent should be within 1/2 of the arc angle.



7. Marking :

7.1 Resistor :


Resistors shall be marked with color coding colors shall be in accordance with JIS C 0802



### Coated Type Kit Resistors (CFR)

8. Packing specification :

8.1 Taping dimension :




Dimensions (mm)

| Type  | Style | O    | P     | L1-L2  | T   | Z      | R | t    | S        |
|-------|-------|------|-------|--------|-----|--------|---|------|----------|
| CR-25 | PT-52 | 52±1 | 5±0.3 | 1 Max. | 6±1 | 1 Max. | 0 | 4 ±1 | 0.5 Max. |


8.2 Bulk in inner box packing ( in plastic Bag )



100 pcs./polybag  
255x0.08x72 (mm) LxHxW



Inner Box of Plastic Bag. (3,000 pcs.)




Carton Box (60,000 pcs.)

Dimension (mm)

| Type  | Q'ty / Bag (pcs.) | Q'ty / Inner Box (pcs.) | Q'ty / Carton (pcs.) | Inner Box Size L x W x H (±5) | Carton Box Size L x W x H (±5) |
|-------|-------------------|-------------------------|----------------------|-------------------------------|--------------------------------|
| CR-25 | 100               | 3,000                   | 60,000               | 262 x 84 x 79                 | 270 x 460 x 350                |





Sample: CR 1/4W +/- 5% 4.7Ω 100 Pcs in Poly bag Resistors → CFR0W4J047JKIT

## Coated Type Kit Resistors (CFR)

### Environment Related Substance

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and Halogen free.

Ozone layer depleting substances.

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFCs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

### Storage Condition

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of  $25^{\circ}\text{C} \pm 5^{\circ}\text{C}$  and a relative humidity of  $60\%RH \pm 10\%RH$

Even within the above guarantee periods, do not store these products in the following conditions. Otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

1. In salty air or in air with a high concentration of corrosive gas, such as  $\text{Cl}_2$ ,  $\text{H}_2\text{S}$ ,  $\text{NH}_3$ ,  $\text{SO}_2$ , or  $\text{NO}_2$
2. In direct sunlight