


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® COLD	53113510 14.11.2013

High cold-resistance
Cold impact resistance
High mechanical stability
Optimum strain relief
Wide, variable clamping ranges



Good chemical resistance



Cold-resistant



Corrosion-resistant



Mechanical resistance



Temperature-resistant

Info

For extreme sub-zero temperatures

Application range

In areas where mechanical stability and high cold-resistance are critical
Air-conditioning technology
Freezing plants, cold storage
Offshore sector
Plant engineering

Design

Metric connection thread acc. to EN 50262

Note

Counter nut to be used: SKINDICHT® SM-M
Refer to SKINTOP® metric accessories for suitable accessories

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® COLD	1 / 3
--------------------	-------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® COLD	53113510 14.11.2013

Technical Data

Article designation / size:	16 x 1,5
Clamping range ØF (mm):	4,5-10
SW (mm):	20
Overall length, C (mm):	32
Thread length, D (mm):	7
Pieces / PU:	100
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Note:	In stainless steel V2A available
Material:	Body: nickel-plated brass Insert: special polyamide Sealing ring: silicone O-ring: silicone
Protection rating:	IP 68 - 10 bar (M12 x 1.5 - M20 x 1.5) IP 68 - 5 bar (M25 x 1.5 - M63 x 1.5)
Temperature range:	-70°C to +100°C

Product Management	Document: SKINTOP® COLD	2 / 3
--------------------	-------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® COLD	53113510 14.11.2013



Product Management	Document: SKINTOP® COLD	3 / 3
--------------------	-------------------------	-------