


"FF15PA" SERIES FAN FILTERS

Description: **Fan Filter 115/230 Va.c.**






- Type of material:** PC/ABS Alloy, PA 66 GF13 HSL for elastic clips
- Standard color:** RAL 7035, other colors on request
- Protection degree:** IP54, according to EN 60529 standard Type 12 according to UL 508 Std
- Fixing system:** by elastic clips, otherwise by four self-threading screws
- Plate thickness:** from 1.5 mm to 2.5 mm
- Storage temperature:** from -45°C to +75°C
- Lifetime L10 at 25°C:** 57,000 h
- Motor protection:** impedance
- Electrical connection:** by terminal block 2 poles L-N
- Earth connection:** (by M4 screw on fan's casing)
- Appliance class:** class I
- Type of filter media:** thermo-linked progressive structure synthetic fibre
- Filtering class:** class G3, according to EN 779
- Degree of separation:** 85% - DIN 24185
- Dust retention capacity:** 600 g/m²
- Note:** filter media is washable about 10 times
- Weight:** 1.2 Kg
- Approvals:** CE, UL E223195, UL E237544

technical drawing



mounting cut-out



Model	Voltage	Frequency	Rated Current	Rated Power	Max Air Flow**	Static Pressure	Noise	Rated Temp. Range	Approvals
	(V)	(Hz)	(A)	(W)	(m ³ /h)	(Pa)	[db(A)]	(°C)	
FF15PA115UF	115 V a.c.	50/60	0.210/0.210	17/16	105/119	54/57	43.0/48.0	-10 ÷ +55	CE; cURus
FF15PA115UFR	115 V a.c.	50/60	0.210/0.210	17/16	106/119	66/70	43.0/48.0	-10 ÷ +55	CE; cURus
FF15PA230UF	230 V a.c.	50/60	0.110/0.100	18/17	105/119	54/57	43.0/48.0	-10 ÷ +55	CE; cURus
FF15PA230UFR	230 V a.c.	50/60	0.110/0.100	18/17	106/119	66/70	43.0/48.0	-10 ÷ +55	CE; cURus

data with uncertainty of 15%

All specifications, data and drawing are subject to change without notice and are approximate. Please refer to our terms of sales including our warranty and limited liabilities clause