

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® COLD-R	53113620 14.11.2013

For the benefits, refer to SKINTOP® COLD



Good chemical resistance



Cold-resistant



Corrosion-resistant



Mechanical resistance



Temperature-resistant



Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Note

Counter nut to be used: SKINDICHT® SM-M

Refer to SKINTOP® metric accessories for suitable accessories

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® COLD-R	1 / 3
--------------------	---------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® COLD-R	53113620 14.11.2013

Technical Data

Article designation / size:	20 x 1,5
Clamping range ØF (mm):	5-10
SW (mm):	24
Overall length, C (mm):	35,5
Thread length, D (mm):	8
Pieces / PU:	50
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Note:	In stainless steel V2A available
Material:	Body: nickel-plated brass Insert: special polyamide Sealing ring: silicone O-ring: silicone
Protection rating:	IP 68 - 10 bar (M12 x 1.5 - M20 x 1.5) IP 68 - 5 bar (M25 x 1.5 - M63 x 1.5)
Temperature range:	-70°C to +100°C

Product Management	Document: SKINTOP® COLD-R	2 / 3
--------------------	---------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® COLD-R	53113620 14.11.2013



Product Management	Document: SKINTOP® COLD-R	3 / 3
--------------------	---------------------------	-------