INNOGOODS BV SAFETY DATA SHEET

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier	PINGI CAR-DEHUMIDIFIER LV-A150 - LV-A300, LV-A350, LV2-A350, 350SDA, LV-	
Name of the substance	B300, LV-B450, LV3-B450, ASB-1000	
	B300, EV-B430, EV3-B430, A3B-1000	
Identification number	-	
Registration number	-	
Synonyms	amorphous silicon dioxide	
Issue date	17-March-2015	
Version number	03	
Revision date	18-March-2018	
1.2. Relevant identified uses of the	substance or mixture and uses advised against	
Identified uses	Desiccant. For adsorption of moisture and prevention of corrosion and mould growth.	
Uses advised against	No other uses are advised.	
1.3. Details of the supplier of the s	afety data sheet	
Manufacturer	Innogoods BV	
Address	Rivium 2e straat 40	
	NL-2909 LG Capelle aan den IJssel	
Country	Netherlands	
Telephone	+31 (0)88- 995 10 03	
Fax	+31 (0)88- 995 10 09	
e-mail	marco@innogoods.nl	
Contact	Marco Verschuur	
Web site	www.pingi.com	
1.4 Emergency telephone	+31 (0)88- 995 10 03 (09:00 - 17:00)	
number		

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The substance has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

This substance does not meet the criteria for classification according to Regulation (EC) 1272/2008 as amended.

Hazard summary	Not classified for health hazards. However, occupational exposure to the mixture or substance(s) may cause adverse health effects. Repeated exposure may cause skin dryness or cracking. Exposure to powder or dusts may be irritating to eyes, nose and throat. This is a consumer care product that is safe for consumers when used according to the label directions. Like many consumer products, a small number of individuals may experience reactions such as	
	redness, rash and / or swelling upon prolonged or repeated skin contact or eye contact.	
2.2. Label elements		
Label according to Regulation (EC) No. 1272/2008 as amended	
Hazard pictograms	None.	
Signal word	None.	
Hazard statements	The substance does not meet the criteria for classification.	
Precautionary statements		
Prevention		
P102	Keep out of reach of children.	

P103 Read label before use.

Response	
P101	If medical advice is needed, have product container or label at hand.
Storage	Store away from incompatible materials.
Disposal	Dispose of waste and residues in accordance with local authority requirements.
Supplemental label information	None.
2.3. Other hazards	This product has the potential for generation of respirable dust during handling and use. Slippery, can cause falls if walked on.

SECTION 3: Composition/information on ingredients

3.1. Substances

General info Chemic	rmation al name	%	CAS-No. / EC No.	REACH Registration No.	INDEX No.	Notes
Silica g	el	100	7631-86-9	01-2120105300-82-0000	-	
			231-545-4			
Cla	ssification: -					

List of abbreviations and symbols that may be used above

#: This substance has been assigned Community workplace exposure limit(s).

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

M: M-factor

SECTION 4: First aid measures

General information	IF exposed or concerned: Get medical advice/attention. Show this safety data sheet to the doctor in attendance.
4.1. Description of first aid measur	res
Inhalation	If dust from the material is inhaled, remove the affected person immediately to fresh air. Call a physician if symptoms develop or persist.
Skin contact	Wash the skin immediately with soap and water. Take off contaminated clothing and wash before reuse. Get medical attention if irritation develops and persists.
Eye contact	Do not rub eyes. Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention if irritation develops and persists.
Ingestion	If swallowed, rinse mouth with water (only if the person is conscious). Drink water as a precaution. If ingestion of a large amount does occur, call a poison control centre immediately.
4.2. Most important symptoms and effects, both acute and delayed	Dusts may irritate the respiratory tract, skin and eyes.
4.3. Indication of any immediate medical attention and special treatment needed	Treat symptomatically.
SECTION 5: Firefighting me	easures
General fire hazards	Not a fire hazard. No unusual fire or explosion hazards noted.
5.1. Extinguishing media Suitable extinguishing media	Use fire-extinguishing media appropriate for surrounding materials.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
5.2. Special hazards arising from the substance or mixture	No unusual fire or explosion hazards noted.
5.3. Advice for firefighters Special protective equipment for firefighters	Wear self-contained breathing apparatus and protective clothing.

Special fire fighting procedures	Move containers from fire area if you can do so without risk. No unusual fire or explosion hazards noted. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel	Wear appropriate protective equipment and clothing during clean-up. Keep unnecessary personnel away.
	Ensure adequate ventilation. Avoid inhalation of dust from the spilled material. Wear a dust mask if dust is generated above exposure limits. In case of spills, beware of slippery floors and surfaces. For personal protection, see section 8.
For emergency responders	As detailed in section for non-emergency personnel. Use personal protection recommended in Section 8 of the SDS.
6.2. Environmental precautions	Avoid release to the environment.
6.3. Methods and material for containment and cleaning up	Stop the flow of material, if this is without risk. Avoid the generation of dusts during clean-up. If sweeping of a contaminated area is necessary use a dust suppressant agent which does not react with the product. Collect dust using a vacuum cleaner equipped with HEPA filter. The product is immiscible with water and will spread on the water surface. Following product recovery, flush area with water
	Large Spills: Wet down with water and dike for later disposal. Shovel the material into waste container. Following product recovery, flush area with water.
	Small Spills: Sweep up or vacuum up spillage and collect in suitable container for disposal.
6.4. Reference to other sections	For personal protection, see section 8. For waste disposal, see section 13 of the SDS.
SECTION 7. Handling and	

SECTION 7: Handling and storage

7.1. Precautions for safe handling	Provide appropriate exhaust ventilation at places where dust is formed. Do not breathe dust from this material. In case of insufficient ventilation, wear suitable respiratory equipment. Avoid contact with skin and eyes. Avoid prolonged exposure. Forms smooth, slippery surfaces on floors, posing an accident risk. Practice good housekeeping.
7.2. Conditions for safe storage, including any incompatibilities	Avoid dust formation. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in air-tight containers- material is hygroscopic. Guard against dust accumulation of this material. Keep out of the reach of children. Store away from incompatible materials (see Section 10 of the SDS).
7.3. Specific end use(s)	The specified uses for this material are shown in section 1 of this document

SECTION 8: Exposure controls/personal protection

8.1. Control parameters Occupational exposure limits **United Kingdom** Form Components Туре Value Silica gel (CAS 7631-86-9) TWA 6 mg/m3 Inhalable dust. 2.4 mg/m3 Respirable dust. **Biological limit values** No biological exposure limits noted for the ingredient(s). **Recommended monitoring** Follow standard monitoring procedures. procedures Derived no-effect level (DNEL) Components Route Value Form Type Silica gel (CAS 7631-86-9) Respirable fraction. Industry Inhalation 4 mg/m3 Predicted no effect Not available. concentrations (PNECs)

8.2. Exposure controls

Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Ventilation should be sufficient to effectively remove and prevent buildup of any dusts or fumes that may be generated during handling or thermal processing. If engineering measures are not sufficient to maintain concentrations of dust particulates below the OEL (occupational exposure limit), suitable respiratory protection must be worn. Ensure adequate ventilation, especially in confined areas.
Individual protection measures, suc	h as personal protective equipment
General information	Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment. Eye wash fountain is recommended. Keep working clothes separately. Launder contaminated clothing before reuse.
Eye/face protection	Wear safety glasses with side shields (or goggles). Avoid contact with eyes. Use tight fitting goggles if dust is generated. (EN166) Eye wash fountain is recommended.
Skin protection	
- Hand protection	Suitable gloves can be recommended by the glove supplier. (EN374) Use protective gloves made of: PVC or other plastic material gloves.
- Other	Normal work clothing (long sleeved shirts and long pants) is recommended. Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.
Respiratory protection	If engineering controls do not maintain airborne concentrations below recommended exposure limits (where applicable) or to an acceptable level (in countries where exposure limits have not been established), an approved respirator must be worn. When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. Respirator type FFP2 or FFP3 (EN 149:2001)
Thermal hazards	None known.
Hygiene measures	Do not get this material in contact with eyes. Do not breathe dust. When using, do not eat, drink or smoke. Avoid contact with eyes. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.
Environmental exposure controls	No special measures required Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Dry flowable granules.
Physical state	Solid.
Form	Granules
	Beads
Colour	White.
Odour	Odourless.
Odour threshold	Not available.
рН	Not applicable
Melting point/freezing point	Not applicable
Initial boiling point and boiling	Not applicable
range	
Flash point	Not applicable.
Evaporation rate	Not applicable
Flammability (solid, gas)	Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower Not applicable (%)

Flammability limit - upper (%)	Not applicable
Vapour pressure	Not applicable
Vapour density	Not applicable
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Insoluble
Solubility (other)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not applicable
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2. Other information	
Bulk density	0.80 - 0.90 g/cm³
Percent volatile	0 % estimated
SECTION 10: Stability and	d reactivity
10.1. Reactivity	Material is stable under normal conditions.
10.0 Obernigel stability	

· · · · · · · · · · · · · · · · · · ·	
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	Hazardous polymerisation does not occur.
10.4. Conditions to avoid	Avoid spread of dust. Avoid conditions which create dust. Contact with incompatible materials. Heat is evolved on contact with water
10.5. Incompatible materials	None known.
10.6. Hazardous decomposition products	No dangerous reaction known under conditions of normal use.

SECTION 11: Toxicological information

General information	Occupational exposure to the substance or mixture may cause adverse effects. This product has no known adverse effect on human health. Data shown in this section has been published in the substance(s) REACH dossier Dust may be slightly irritating to eyes and respiratory tract. Prolonged skin contact may cause skin irritation and/or dermatitis.
Information on likely routes of exposi-	sure
Inhalation	Dust may irritate respiratory system. Prolonged inhalation may be harmful.
Skin contact	Dust or powder may irritate the skin.
Eye contact	Dust in the eyes will cause irritation.
Ingestion	Not classified.
Symptoms	Possible irritant effects. Dusts may irritate the respiratory tract, skin and eyes.

11.1. Information on toxicological effects

Components	Species	Test results
Silica gel (CAS 7631-86-9)		
Acute		
Dermal		
LD50	Rabbit	> 5000 mg/kg Occluded (dermal)
Inhalation		
LC0	Rat	>= 0.69 mg/l, 4 hours
Oral		
LD50	Rat	> 5000 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Not irritating: OECD 404
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met. Dust in the eyes will cause irritation.
Respiratory sensitisation	Due to partial or complete lack of data the classification is not possible.
Skin sensitisation	Based on available data, the classification criteria are not met. Frequent or prolonged contact may defat and dry the skin, leading to discomfort and dermatitis.
Germ cell mutagenicity	Due to partial or complete lack of data the classification is not possible.
Carcinogenicity	Due to partial or complete lack of data the classification is not possible.
IARC Monographs. Overall Ev	valuation of Carcinogenicity
Silica gel (CAS 7631-86-9	9) 3 Not classifiable as to carcinogenicity to humans.
Reproductive toxicity	Due to partial or complete lack of data the classification is not possible.
Specific target organ toxicity - single exposure	Due to partial or complete lack of data the classification is not possible.
Specific target organ toxicity - repeated exposure	Due to partial or complete lack of data the classification is not possible.
Aspiration hazard	Not applicable.
Mixture versus substance information	Not applicable.
Other information	This product has no known adverse effect on human health.

SECTION 12: Ecological information

12.1. Toxicity	Not expected to be harmful to aquatic organisms.		
Components		Species	Test results
Silica gel (CAS 7631-86-9)			
Aquatic			
Algae	NOEL	Algae	> 10000 mg/l, 72 hours
Crustacea	EC50	Daphnia	> 10000 mg/l, 24 hours
Fish	LC0	Zebra danio (Danio rerio)	> 10000 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

12.2. Persistence and degradability	The product solely consists of inorganic compounds which are not biodegradable.
12.3. Bioaccumulative potential	Does not bioaccumulate.
Partition coefficient n-octanol/water (log Kow)	Not applicable. (inorganic substance)
Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	Insoluble and thus presents a low mobility in most soils
Mobility in general	The product is immiscible with water and will sediment in water systems.
12.5. Results of PBT and vPvB assessment	Not applicable. PBT/vPvB assessment not available as chemical safety assessment not required/not conducted
12.6. Other adverse effects	Based on available data, there is no evidence of significant toxicity of Synthetic Amorphous Silica to environmental organisms.

SECTION 13: Disposal considerations

13.1. Waste treatment methods	
Residual waste	Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions). Dispose of in accordance with local regulations. Material should be recycled if possible.
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Where possible recycling is preferred to disposal or incineration. Dispose of as unused product.

EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

Not regulated as dangerous goods.

RID

Not regulated as dangerous goods.

ADN

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

14.7. Transport in bulk accordingNot applicable.to Annex II of MARPOL 73/78and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended Not listed.

Regulation (EC) No. 850/2004 on persistent organic pollutants, Annex I

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended Not listed.

- Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended Not listed.
- Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry

Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006 Annex XVII Substances subject to restriction on marketing and use

Not regulated.

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended Not listed.

Directive 2004/37/EC: on the protection of workers from the risks related to exposure to carcinogens and mutagens at work Not listed.

Directive 2004/37/EC on the protection of workers from the risks related to exposure to carcinogens and mutagens at work Not regulated.

Directive 92/85/EEC: on the safety and health of pregnant workers and workers who have recently given birth or are breastfeeding.

Not regulated.

Other EU regulations		
-	or accident hazards involving dangerous substances	
Not listed.		
	ptection of the health and safety of workers from the risks related to ch	emical agents at work.
Always applicable.	- -	-
Directive 94/33/EC on the pro	otection of young people at work	
Not listed.		
Other regulations	This Safety Data Sheet complies with the requirements of Regulation amended.	
	Prepared in accordance with Annex II of the REACH Regulation (EC Commission Regulation (EU) 2015/830), and with CLP Regulation The product is classified and labelled in accordance with EC directi This product is in compliance with Directive 2011/65/EU on the rest hazardous substances in electrical and electronics equipment (RoF	(EC) 1272/2008 ves or respective national laws. riction of the use of certain
National regulations	Follow national regulation for work with chemical agents.	
15.2. Chemical safety assessment	Chemical Safety Assessment has been carried out.	
International Inventories		
Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of New and Existing Chemicals (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
		N/

United States & Puerto Rico Toxic Substances Control Act (TSCA) Inventory A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

SECTION 16: Other information

List of abbreviations	Not available.
References	Not available.
Information on evaluation method leading to the classification of mixture	Not applicable.
Full text of any H-statements not written out in full under Sections 2 to 15	None.
Revision information	This document has undergone significant changes and should be reviewed in its entirety.
Training information	Follow training instructions when handling this material.
Disclaimer	The information in the sheet was written based on the best knowledge and experience currently available.
	MANUFACTURER DISCLAIMER: The information given within this SDS is correct to the best of our knowledge, information and belief at the date of its revision and publication. However, the manufacturer makes no representation, warranty or guarantee as to its accuracy, reliability or completeness, nor assumes any liability for its use. It is the user's responsibility to confirm in advance that the information is current, applicable and suitable to their circumstances for each particular use. No representative of ours has authority to waive this provision. Please call for document accuracy if the revision date has exceeded 3 years.

Yes