

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® DIX-M	53340969 14.11.2013


Easy insertion of several cables into one gland
Higher packing density allows smaller part construction



Automation



Assembly time




Optimum strain relief



Temperature-resistant



UV-resistant



Application range

For use in SKINTOP® cable glands.

A sealing ring with several holes is used in place of the inner sealing insert.

Design

SKINTOP® DIX-M VITON® is resistant to oil, water, alkaline solutions, acids, solvents etc.

Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs

Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	40969
Size M:	M 40
Number of cables x cable Ø:	9 x 6,9
Pieces / PU:	25
On request:	Special shapes
Colour delivered:	Black, RAL 9005
Material:	NBR VITON®
Protection rating:	IP 54
Temperature range:	-40°C to +100°C

Product Management	Document: SKINTOP® DIX-M	1 / 1
--------------------	--------------------------	-------