

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® K-M ATEX plus	54115240 04.04.2014

High degree of protection
Cold impact resistance
High strain relief
Wide, variable clamping ranges
Permanent vibration protection



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

Application range

Devices, machines and apparatus of enhanced safety protection type "e"
Equipment group II / Category 2G+1D
For mobile applications in offshore and marine industries
Chemical and petrochemical industry

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® K-M ATEX plus	1 / 3
--------------------	----------------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® K-M ATEX plus	54115240 04.04.2014

Technical Data

Article designation / size:	K-M 32 ATEX plus
Clamping range ØF (mm):	12-21
Thread M:	32 x 1.5
SW (mm):	36
Overall length, C (mm):	39 - 47
Thread length, D (mm):	10
Pieces / PU:	25
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEx IBE 13.0027X
Colour delivered:	RAL 9005 black/UV-resistant
Material:	Body: special polyamide Seal: special elastomer O-ring: CR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-20°C to +80°C

Product Management	Document: SKINTOP® K-M ATEX plus	2 / 3
--------------------	----------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® K-M ATEX plus	54115240 04.04.2014



Product Management	Document: SKINTOP® K-M ATEX plus	3 / 3
--------------------	----------------------------------	-------