

Supplier	Article description	Art. No. / GTIN	Warranty	
<b>T.I.P.</b> <b>Technische Industrie Produkte GmbH</b> <b>Siemensstr. 17</b> <b>74915 Waibstadt</b>  <b>Tel.: 07263-9125-0</b> <b>Fax: 07263-9125-25</b>  <b>www.tip-pumpen.de</b>	<b>submersible dirty water pump</b> <b>MAXIMA 400 CX</b>	<b>30140</b>	<b>24 Months</b>	
		4011458301409		
	<b>Master Box Information</b>			
	<b>Master Box dimensions in cm</b>			<b>weight (kg) gross</b>
	<b>Width</b>	<b>Depth</b>	<b>Height</b>	
41.6	23.0	52.5	25.7	2
<b>Article Information</b>				
<b>Color Box dimensions in cm</b>			<b>weight (kg) net / gross</b>	
<b>Width</b>	<b>Depth</b>	<b>Height</b>		<b>Qty.</b>
20.0	19.0	45.5	11.3 / 12.6	1
<b>submersible dirty water pump</b> <b>MAXIMA 400 CX</b>		<b>quantity / pallet:</b>		<b>62</b>
		<b>quantity / truck:</b>		<b>2.046</b>

**Description:**

The specially designed dirty water pump is characterized by high capacity and exceptional strength. Because of the high standards at construction and waste water pits, the pump and the almost indestructible impeller are completely made of high quality cast iron. Typical applications include: emptying of ponds, tanks, reservoirs, waste water pits and emergency drainage as a result of flooding or flood. With an adjustable float switch for manual and automatic operation.

**Technical Data:**

Motor	950 W
Max. delivery height / pressure	9 m / 0.9 bar
Max. flow rate	24,000 L/h
Pressure connection	45.48 mm (1½", female)
Min. suction level	40 mm
Max. grain size	35 mm
Max. submersion depth	7 m
Connection hose	10 m / H07RN-F
Max. Temp. Medium	35°C
Pump housing	stainless steel / cast iron
Impeller	cast iron



**Approval marks:**

