

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS	52015766 14.11.2013

Maximum reliability
Optimum strain relief
Wide, variable clamping ranges



Good chemical resistance



Corrosion-resistant



Optimum strain relief



Robust



Temperature-resistant



Variety of approval certifications



Application range

In areas where mechanical and chemical stability are critical
Chemical industry
Measurement and control technology
Machine and equipment manufacturing
Plant engineering

Design

PG connection thread

Note

Counter nut to be used: SKINDICHT® SM
Refer to SKINTOP® PG accessories for suitable accessories

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® MS	1 / 3
--------------------	-----------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS	52015766 14.11.2013

Technical Data

Article designation / size:	MS 42
Clamping range ØF (mm):	28 - 38
SW (mm):	57
Overall length, C (mm):	62
Thread length, D (mm):	15
Pieces / PU:	5
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	IP 68 - 5 bar
Temperature range:	-30°C to +100°C

Product Management	Document: SKINTOP® MS	2 / 3
--------------------	-----------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS	52015766 14.11.2013



Product Management	Document: SKINTOP® MS	3 / 3
--------------------	-----------------------	-------