

U.I. Lapp GmbH	DATASHEET	
	SKINTOP® MS-IS-M	53112780 14.11.2013

Short connection thread for more space inside the industrial connectors
Wide, variable clamping ranges
Optimum strain relief



Industrial machinery and plant engineering



Optimum strain relief



Robust



Connector with standard housing unit



Temperature-resistant

Application range

Specially designed for use on industrial connectors.

Design

Metric connection thread acc. to EN 50262

Note

For suitable multiple seal inserts please see SKINTOP® DIX PG 21 (25 x 1.5) and DIX PG 29 (32 x 1.5)

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® MS-IS-M	1 / 3
--------------------	----------------------------	-------


U.I. Lapp GmbH	DATASHEET	
	SKINTOP® MS-IS-M	53112780 14.11.2013

Technical Data

Article designation / size:	25 x 1,5
Clamping range ØF (mm):	11-18
SW (mm):	30
Overall length, C (mm):	37
Thread length, D (mm):	5
Pieces / PU:	25
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	IP 68 - 5 bar
Temperature range:	-30°C to +100°C

Product Management	Document: SKINTOP® MS-IS-M	2 / 3
--------------------	----------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	SKINTOP® MS-IS-M	53112780 14.11.2013



Product Management	Document: SKINTOP® MS-IS-M	3 / 3
--------------------	----------------------------	-------