

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS-M ATEX	53112810 04.04.2014

Cold impact resistance
High strain relief
Wide, variable clamping ranges
Anti-static
Maximum reliability



Good chemical resistance



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

Application range

Devices, machines and apparatus of enhanced safety protection type "e"
Equipment group II / Category 2G+1D
For mobile applications in offshore and marine industries
Chemical and petrochemical industry

Design

Metric connection thread acc. to EN 50262

Norm references / Approvals

UL File Nr. E79903

Note

Refer to SKINTOP® SDV-M ATEX for suitable accessories

Product features

SKINTOP® MS-M-XL ATEX is similar to the SKINTOP® MS-M ATEX, but has an extended connection thread for thick walls

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® MS-M ATEX	1 / 3
--------------------	------------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS-M ATEX	53112810 04.04.2014

Technical Data

Article designation / size:	16 x 1,5
Clamping range ØF (mm):	4,5 - 10
SW (mm):	20
Overall length, C (mm):	37
Thread length, D (mm):	12
Pieces / PU:	100
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEx IBE 13.0026X
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-30°C to +90°C

Product Management	Document: SKINTOP® MS-M ATEX	2 / 3
--------------------	------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS-M ATEX	53112810 04.04.2014



Product Management	Document: SKINTOP® MS-M ATEX	3 / 3
--------------------	------------------------------	-------