

U.I. Lapp GmbH	DATASHEET	
	SKINTOP® MS-NPT BRUSH	53112077 14.11.2013

Faster, easier screen contact
Optimum, low-resistance 360° screen contact
Faster than any other comparable system
Uncomplicated and reliable
Maximum assembly freedom during adjustment



Reliability



Interference signals



Temperature-resistant



Variety of approval certifications

Application range

For EMC-compliant earthing of the copper braiding, or for cables with copper shaft sheath
Automation technology
Conveyor technology
High-power drives
Frequency converters

Design

NPT connection thread acc. to ANSI B1.20.2 - 1983

Norm references / Approvals

UL File Nr. E79903

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	2"
Clamping range ØF (mm):	34 - 45
SW (mm):	67
Overall length, C (mm):	63
Thread length, D (mm):	17
Pieces / PU:	1
Material:	Body: nickel-plated brass EMC brush: brass Sealing ring: special elastomer O-ring: special elastomer
Protection rating:	IP 68 - 5 bar
Temperature range:	-30°C to +100°C

Product Management	Document: SKINTOP® MS-NPT BRUSH	1 / 2
--------------------	---------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS-NPT BRUSH	53112077 14.11.2013



Product Management	Document: SKINTOP® MS-NPT BRUSH	2 / 2
--------------------	---------------------------------	-------