

U.I. Lapp GmbH	DATASHEET	
	SKINTOP® MSR-M	53112511 14.11.2013

For the benefits, refer to SKINTOP® MS-M




Corrosion-resistant



Mechanical resistance



Optimum strain relief



Acid-resistant



Temperature-resistant



Variety of approval certifications



Info

SKINTOP® MSR-M 75 x 1.5 with innovative double lamella gasket for easier assembling of cables with large diameters. Now with IP 69 K approval! Proven to withstand the most demanding cleaning procedures for industrial machinery with high-pressure cleaners and hot water!

Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Norm references / Approvals

UL File Nr. E79903

Note

Counter nut to be used: SKINDICHT® SM-M

Refer to SKINTOP® metric accessories for suitable accessories

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® MSR-M	1 / 3
--------------------	--------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MSR-M	53112511 14.11.2013

Technical Data

Article designation / size:	75 x 1,5
Clamping range ØF (mm):	53-63
SW (mm):	95
Overall length, C (mm):	105
Thread length, D (mm):	15
Pieces / PU:	1
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Approvals:	IP 69 K approval from size M75 x 1.5 pending. UL, CSA, DNV and VDE approval for sizes M90 x 2 to M110 x 2 pending.
Note:	In stainless steel V2A available
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	IP 68 IP 69 K
Temperature range:	Dynamic: -30 °C to +100 °C Fixed: -40 °C to +100 °C

Product Management	Document: SKINTOP® MSR-M	2 / 3
--------------------	--------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MSR-M	53112511 14.11.2013



Product Management	Document: SKINTOP® MSR-M	3 / 3
--------------------	--------------------------	-------