

U.I. Lapp GmbH	DATASHEET	
	SKINTOP® MSR-M-XL	53112155 14.11.2013


For the benefits, refer to SKINTOP® MS-M-XL




Corrosion-resistant



Mechanical resistance



Optimum strain relief



Acid-resistant



Temperature-resistant



Variety of approval certifications



Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Norm references / Approvals

UL File Nr. E79903

Note

Counter nut to be used: SKINDICHT® SM-M

Refer to SKINTOP® metric accessories for suitable accessories

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® MSR-M-XL	1 / 3
--------------------	-----------------------------	-------


U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MSR-M-XL	53112155 14.11.2013

Technical Data

Article designation / size:	40 x 1,5
Clamping range ØF (mm):	15-23
SW (mm):	45
Overall length, C (mm):	53,5
Thread length, D (mm):	15
Pieces / PU:	10
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Note:	In stainless steel V2A available
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	Remark: A RoHS-non-compliant version is marketed under ÖLFLEX® 110 with VDE-REG.-Nr. 8067. To order this, please add appendix <1> to the below stated part numbers. This does not affect the above given further technical data or description. IP 69 K IP 68 - 10 bar
Temperature range:	Dynamic: -30 °C to +100 °C Fixed: -40 °C to +100 °C

Product Management	Document: SKINTOP® MSR-M-XL	2 / 3
--------------------	-----------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MSR-M-XL	53112155 14.11.2013



Product Management	Document: SKINTOP® MSR-M-XL	3 / 3
--------------------	-----------------------------	-------