

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS-SC NPT	53112950 14.11.2013

Highly conductive, flexible EMC contact for clamping various screen diameters
Low-resistance screen contact, optimum EMC protection
Also suitable for continuing the cable screen to another connection
Suitable for cables with and without inner sheath



Reliability



Interference signals



Temperature-resistant



Variety of approval certifications

Application range

For EMC-compliant earthing of the copper braiding, or for cables with copper shaft sheath
Automation technology
Telecommunication
Measurement and control technology
Industrial machinery and plant engineering

Design

NPT connection thread acc. to ANSI B1.20.2 - 1983

Norm references / Approvals

UL File Nr. E79903

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	1 1/4"
Clamping range ØF (mm):	19 - 28
SW (mm):	45
Overall length, C (mm):	57,5
Thread length, D (mm):	17
Pieces / PU:	10
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	IP 68 - 5 bar
Temperature range:	-30°C to +100°C

Product Management	Document: SKINTOP® MS-SC NPT	1 / 2
--------------------	------------------------------	-------

U.I. Lapp GmbH	DATASHEET	 LAPP GROUP
	SKINTOP® MS-SC NPT	53112950 14.11.2013



Product Management	Document: SKINTOP® MS-SC NPT	2 / 2
--------------------	------------------------------	-------