

ICP341018PM

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V
Safety Circuit

Specifications

Renata Type	ICP341018
IEC Designation	ICP041120
Part Number	100730
Contact:	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	35 mAh
Minimum Capacity	33 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 980 mΩ / 50% SOC

Thickness (t)	Max 3.7 mm
Length (l)	Max 19.5 mm
Width (w)	Max 10.2 mm
Weight	~ 1.7 g


Charging Characteristic	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 17.5 mA
Max. Charging Current	1.0 C CC – 35 mA
Temperature at Charging	0 °C 45 °C

Discharge Characteristic	
Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 70 mA (for non continues discharge) 1.0 C – 35 mA (for continues discharge)
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.