



**G&G Trading International B.V.**

Industrieweg 18-9  
3846 BD Harderwijk  
Tel.+31(0)341-414993  
Fax+31(0)341-419625

[www.spita.eu](http://www.spita.eu)

Rabobank rek.nr.: 13.73.22.828  
K.v.K. Oost Nederland: 08179628  
BTW/VATnr.: NL-8197.70.115.B.01

### SPITA ResQ-tape specifications

Properties	Test method / Norm*	Test results**
Operating temperature	Continue	-60° C up to 260° C
Temperature range	Average	-65° C up to 260° C
Cold brittle point	ASTM D-2137	-65° C
Durometer hardness	Shore Durometer 50-60	58 (24 h room temperature)
Specific Gravity	1.11 – 1.17	1.15
Modulus @ 100%, psi	Continue	203
Tensile strength	ASTM D-412 (950 psi)	1412 psi (97 Bar)
Ultimate elongation	ASTM D-412 (300%)	453% average
Tear resistance	ASTM D-412	5,86 Bar
Pressure resistance	Average	11,5 Bar
Water absorption	Fed.Std601 (3% max)	0,18% average
Dielectric strength	ASTM D-419 (400 per mil)	644 per mil

\* The values (when stated) are the minimum requirements to pass the test.

\*\* The results are coming from two leading test institutes (SGS - USA and TÜV TNO - The Netherlands). The test reports are available on request.

**Available colours 1” rolls (25,4mm x 3,65m x 0,5mm):**  
black, red, clear, white, blue, green, yellow, brown, orange, grey

**Available colours 2” rolls (50,8mm x 3,65m x 0,5mm):**  
black, red, clear, white, blue, green, yellow, brown, orange, grey