

DATA SHEET

UNITRONIC® BUS FD P CAN UL/CSA 2 x 2 x 0,5 mm²

valid from:

06.06.2008

2170279

Application

UNITRONIC® BUS FD P CAN UL/CSA is a highly flexible data cable with UL and CSA approval, for CAN (Controller Area Network) fieldbus system according to ISO11898 as well as for high performance data networks with 120 Ohms nominal impedance. The second pair can be used for electrical power supply for the logical bus units. The transmission characteristics of the cable conform to the CAN system and guarantee a high operating security during data transmission.

UNITRONIC® BUS FD P CAN UL/CSA is intended for high flexible application in power chains, or permanently moving machines, in dry and damp interiors and in harsh industrial environment.

Approval: UL / CSA Type CMX according to UL 444 and CSA C22.2 No.214-02.

Design

fine-wire stranded, 0.5mm² (20AWG) of bare copper Conductor

Insulation foam skin, core diameter approx. 2.4 mm

Coding non-woven tape

Screening braid of tinned copper wires

Sheath PUR, halogen free, flame retardant, violet, OD approx. 10.8 mm

Electrical properties at 20°C

Loop resistance Insulation resistance		max. Ω/km min. GΩxkm	77.8 5
Mutual capacitance	at 800 Hz	nom. nF/km	40
Impedance	at 1 MHz	Ω	120 ± 15
Line attenuation	at 100 kHz	nom. dB/100 m	0.35
	at 1 MHz	nom. dB/100 m	1.1
	at 5 MHz	nom. dB/100 m	2.9
	at 10 MHz	nom. dB/100 m	4.1
	at 20 MHz	nom. dB/100 m	6.2
Near end cross talk attenuation (N	IEXT) at 20 MHz	min. dB	40
Nominal velocity of propagation		%	76
Signal delay		ns/m	4,4
Transfer impedance	at 10 MHz	max. $m\Omega/m$	250
Peak operation voltage (not fo	250		
Test voltage co	ore/core	$U_{eff} \; V$	1500
core/scree	n	$U_{eff}^{or} V$	1000

Mechanical and thermal characteristics

Minimum bend radius	moved	cable diameter x	15
Permissible temperature range	moved	$^{\circ}$	- 30 to + 70
	static	$^{\circ}$	- 40 to + 80
Flame propagation	flame retardant	t acc. to IEC 60 332-1-2	UL 1581 VW-1

elaborated by:	_		
TE-K: P. Samek	Document:	DB2170279EN.doc	page 1 of 1

Nr.: 0019/0894