



UNITRONIC® FD P plus

DB0028650

valid from: 11.02.2011

Application

UNITRONIC® FD P plus is a high flexible data cable with an outer sheath of PUR.

The cable with low capacitance is designed especially for use in power chains, automatic manipulators, in permanently moved machines parts.

The cable is increased oil-, abrasion- and cut resistant, in addition microbe- and hydrolysis resistant. It is cold-resistant and for harsh environmental conditions.

Design

Conductor	superfine wire strands of bare copper wires
Insulation	special Polyolefin-based compound
Core identification code	according to DIN 47100
Stranding	cores stranded in layers, wrapping with fleece on the outer layer
Outer sheath	special PUR-based compound, flame retardant, halogen free colour: grey (RAL 7001)

Electrical properties at 20°

Specific insulation resistance	> 5 G Ω x km
Mutual capacitance	C/C approx. 60 nF/km
Inductivity	approx. 0.65 mH/km
Peak working voltage	250 V (not for power applications)
Test voltage	C/C: 1500 V

Mechanical and thermal properties

Bending radius	5 x cable \emptyset
Temperature range	Flexing: - 40 °C up to +80 °C Fixed installation: - 40 °C up to +80 °C
Flammability	flame retardant acc. to IEC 60 332-1-2

Design based on standard VDE 0812