




MB322-508MRoHS
Compliant

□ □ : Poles

508 : Pitch 5.08mm

322 : Standard

MB : Type

PCB Layout

Pitch : 5.08mm(0.200inch)

Poles	A(mm)	A(inch)	Poles	A(mm)	A(inch)
2	10.16	0.400	15	76.20	3.000
3	15.24	0.600	16	81.28	3.200
4	20.32	0.800	17	86.36	3.400
5	25.40	1.000	18	91.44	3.600
6	30.48	1.200	19	96.52	3.800
7	35.56	1.400	20	101.60	4.000
8	40.64	1.600	21	106.68	4.200
9	45.72	1.800	22	111.76	4.400
10	50.80	2.000	23	116.84	4.600
11	55.88	2.200	24	121.92	4.800
12	60.96	2.400	25	127.00	5.000
13	66.04	2.600			
14	71.12	2.800			

Current rating : 16Amp AC300V

Insulation withstands volt : AC2000V min

Insulation resistance : >2000MΩ DC500V

Operation temperature : -40°C to +105°C

Wire strip length : 4mm~5mm

Wire range : 12~26 AWG

Screw torque : 5.0 lb-inch

DECA
SwitchLab

Switchlab INC.

	Material	Plating/Finish	Remark
1	Insulating body	Polyamide 66(UL94V-0)	Green
2	Cage clamp	Brass	Ni plated
3	Terminal	Brass	Tin plated
4	Screw	Steel	Ni plated