

## **Technisches Datenblatt „80 1-stg. Gewebeklebeband“ Neon Technical data sheet „80 one sided Duct Cloth Tape“ fluorescent**

### **Product Description**


Low-gloss finished PE coated fluorescent cloth tape with a rubber based adhesive.  
High quality purpose for irregular surface, stationery, dance club, floor.

### **Technical Data**

Article No.	CAKK 80M-FL
Backing	PE coated cloth
Adhesive-base	Natural rubber
Total thickness	0,3 mm
Peel adhesion	0,7 kg/25 mm
Rewinding force	4 kg/50 mm
Tensile strength	16 kg/25 mm
Holding power	20 min (25 mm x 25 mm / 40°C)
Ball tack	20 cm / ball no. 20
Temperature resistance	-35 / up to +80 (1h/°C)
Storage life	6 months (20°C / 60%)

The used test methods are based on acceptable specifications like PSTC or internal test methods which are required on request.

## Product Design



### REMARK:

All the technical data are average values. We advice to test the material required to ensure the suitability of intended application. The company reserves the right to improve products and change specifications which may alter performance.

The Statements in this information sheet are based upon our knowledge and practical experience. This data is intended only as a source of information and is given without guarantee and does not constitute a warranty. Suggestion for use and final results on our best technical experiences but cannot be intended as our commitment or liability. The company reserves the right to modify or change the products at any time without notice. All information has to be intended as generic advise for the use of products. Users have to verify the suitability of each tape in actual application under specific conditions.