2.0x1.25mm SMD CHIP LED LAMP

Part Number: KPHCM-2012QBC-D Blue



ATTENTION OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC DISCHARGE SENSITIVE DEVICES

Features

- 2.0X1.25mm SMT LED,0.5mm max. thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package : 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

Description


The Blue source color devices are made with InGaN Light Emitting Diode.

Static electricity and surge damage the LEDS.

It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.

All devices, equipment and machinery must be electrically grounded.

Package Dimensions



SPEC NO: DSAE6004 APPROVED: WYNEC REV NO: V.6B CHECKED: Allen Liu DATE: MAR/30/2013 DRAWN: F.Cui PAGE: 1 OF 5 ERP: 1203003841

Salaatian Cuida

Part No.	Dice	Lens Type	lv (mo @ 2	/ - -	•••	
			Min.	Тур.	201/2	
KPHCM-2012QBC-D	Blue (InGaN)	Water Clear	40	100	110°	

Notes:

1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

2. Luminous intensity/ luminous Flux: +/-15%.

3. Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Blue	460		nm	IF=20mA
λD [1]	Dominant Wavelength	Blue	465		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Blue	25		nm	IF=20mA
С	Capacitance	Blue	100		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Blue	3.3	4	V	IF=20mA
lr	Reverse Current	Blue		50	uA	Vr=5V

Notes:


Wavelength: +/-1nm.
Forward Voltage: +/-0.1V.
Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C

Parameter	Blue	Units	
Power dissipation	120	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	150	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		

Note:


1. 1/10 Duty Cycle, 0.1ms Pulse Width.



KPHCM-2012QBC-D


Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.


Reflow Soldering Profile For Lead-free SMT Process.




NOTES: 1.We recommend the reflow temperature 245°C(+/-5°C).The maximum soldering temperature should be limited to 260°C. 2.Don't cause stress to the epoxy resin while it is exposed to bit temperature to high temperature. 3.Number of reflow process shall be 2 times or less.








Reel Dimension





REV NO: V.6B CHECKED: Allen Liu

DATE: MAR/30/2013 DRAWN: F.Cui

PAGE: 4 OF 5 ERP: 1203003841

