

3.2x1.6mm SMD CHIP LED LAMP

Part Number: KPTD-3216SYCK

Super Bright Yellow


Features


- 3.2mmX1.6mm SMT LED, 1.8mm thickness.
- Low power consumption.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel .
- Moisture sensitivity level : level 3.
- RoHS compliant.

Description

The Super Bright Yellow device is made with AlGaInP (on GaAs substrate) light emitting diode chip.

Package Dimensions





- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.2(0.008")$ unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
 The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAA4411 **REV NO: V.17B DATE: MAR/20/2013** PAGE: 1 OF 5 CHECKED: Allen Liu APPROVED: WYNEC ERP: 1203002312 DRAWN: Q.M.Chen

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KPTD-3216SYCK	Super Bright Yellow (AlGaInP)	Water Clear	700	800	35°

Notes:

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 2. Luminous intensity/ luminous Flux: +/-15%.
 3. Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Yellow	590		nm	IF=20mA
λD [1]	Dominant Wavelength	Super Bright Yellow	590		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Yellow	20		nm	IF=20mA
С	Capacitance	Super Bright Yellow	20		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Super Bright Yellow	2	2.5	V	IF=20mA
lR	Reverse Current	Super Bright Yellow		10	uA	V _R =5V

Notes:


- 1.Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C


Parameter	Super Bright Yellow		
Power dissipation	75	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	175	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		


Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAA4411 **REV NO: V.17B DATE: MAR/20/2013** PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Q.M.Chen ERP: 1203002312





Super Bright Yellow KPTD-3216SYCK











40° 50° 60°


SPATIAL DISTRIBUTION

SPEC NO: DSAA4411 **REV NO: V.17B** DATE: MAR/20/2013 PAGE: 3 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** ERP: 1203002312 DRAWN: Q.M.Chen

KPTD-3216SYCK

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

 1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.
- to high temperature.

 3.Number of reflow process shall be 2 times or less.


Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)



Reel Dimension



Tape Dimensions (Units : mm)





 SPEC NO: DSAA4411
 REV NO: V.17B
 DATE: MAR/20/2013
 PAGE: 4 OF 5


 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Q.M.Chen
 ERP: 1203002312

PACKING & LABEL SPECIFICATIONS

KPTD-3216SYCK







Detailed application notes are listed on our website. http://www.kingbright.com/application notes

SPEC NO: DSAA4411 APPROVED: WYNEC REV NO: V.17B CHECKED: Allen Liu DATE: MAR/20/2013 DRAWN: Q.M.Chen PAGE: 5 OF 5 ERP: 1203002312