

3.2x1.6mm SMD CHIP LED LAMP

Part Number: KPTD-3216CGCK Green


Features


- 3.2mmX1.6mm SMT LED, 1.8mm thickness.
- Low power consumption.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel .
- Moisture sensitivity level : level 3.
- RoHS compliant.

Description

The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode.

Package Dimensions





- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.2(0.008")$ unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
 The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAA8108 **REV NO: V.20B** DATE: APR/06/2013 PAGE: 1 OF 5 CHECKED: Allen Liu APPROVED: WYNEC ERP: 1203002217 DRAWN: Q.M.Chen

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KPTD-3216CGCK	Green (AlGaInP)	Water Clear	120	300	35°

- 1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 2. Luminous intensity/ luminous Flux: +/-15%.
 3. Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	574		nm	IF=20mA
λD [1]	Dominant Wavelength	Green	570		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	20		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Green	2.1	2.5	V	I=20mA
lr	Reverse Current	Green		10	uA	V _R =5V

Notes:


- 1.Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C

Parameter	Green	Units	
Power dissipation	75	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	150	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		

Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.

SPEC NO: DSAA8108 **REV NO: V.20B** DATE: APR/06/2013 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Q.M.Chen ERP: 1203002217




SPEC NO: DSAA8108 REV NO: V.20B DATE: APR/06/2013 PAGE: 3 OF 5
APPROVED: WYNEC CHECKED: Allen Liu DRAWN: Q.M.Chen ERP: 1203002217

KPTD-3216CGCK

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

 1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

 3.Number of reflow process shall be 2 times or less.


Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)



Reel Dimension




Tape Dimensions (Units: mm)





SPEC NO: DSAA8108 REV NO: V.20B DATE: APR/06/2013 PAGE: 4 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Q.M.Chen ERP: 1203002217

PACKING & LABEL SPECIFICATIONS

KPTD-3216CGCK







Detailed application notes are listed on our website. http://www.kingbright.com/application_notes

SPEC NO: DSAA8108 APPROVED: WYNEC REV NO: V.20B CHECKED: Allen Liu DATE: APR/06/2013 DRAWN: Q.M.Chen PAGE: 5 OF 5 ERP: 1203002217