


**Part Number: GC3817**  
**Reed Switch - Compact - Normally Open Contacts**  
**Product Data Sheet**



**PICTURE**



**DIMENSIONS**



File # E103299

✓ RoHS Compliant

Drawings not to scale.  
 All dimensions in mm (inches) nominal.

**SPECIFICATION**

Contact Form		Form A (Normally Open)
Contact Material		Rhodium
Switching Capacity	Max.	60 W/VA
Switching Voltage	Max.	400 VAC / DC
Switching Current	Max.	3.0 A
Carrying Current	Max.	4.0 A
Dielectric Strength	Min.	1000 VDC at >50 AT / 850 VDC at <50 AT
Contact Resistance	Max.	100 mΩ
Insulation Resistance	Min.	10 <sup>11</sup> Ω
Pull - In Sensitivity		30 - 80 AT
Drop - Out Sensitivity	Min.	15 AT
Bounce Time	Max.	0.5 ms
Release Time	Max.	0.10 ms
Resonant Frequency	Typ.	2400 Hz
Operating Frequency	Max.	200 Hz
Vibration (10-1000Hz)		35 g
Shock (11 ms)		50 g
Capacitance	Typ.	0.5 pF
Operate Temperature Range	Deg.	-40°C + 125°C
Test Coil	Type	1800

**NOTE**

- When cutting or bending switch leads it is important that the glass seal is not damaged. The cutting or bending point should be no closer than 3mm (0.118in.) to the glass to metal seal and the lead should be supported between the cutting or bending point and the glass to metal seal.
- We offer a crop and form service for Reed Switches to be customized to your specification.

**ORDERING INFORMATION**

**PART NUMBER GC3817 30 80**

- Type \_\_\_\_\_
- Minimum (AT) Sensitivity \_\_\_\_\_
- Maximum (AT) Sensitivity \_\_\_\_\_

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

**Phone: (1) 973 777 6900**

**www.comus-intl.com**

**Fax: (1) 973 777 8405**

Belgium: + 32 (0)12 390400 - Comus Europe Ltd (Assemtch) UK: +44 (0) 1255 862236 - Germany: +49 (0)911 923 15 943  
 ©2013 Copyright Comus International, 454 Allwood Road, Clifton NJ 07012, USA

An ISO 9001 Certified Company