

## Polypropylene (PP) Film and Foil Capacitors for Pulse Applications in PCM 5 mm

### Special Features

- Pulse duty construction
- Close tolerances up to  $\pm 2.5\%$  ( $\pm 1\%$  on request)
- Very low dissipation factor
- Negative capacitance change versus temperature
- Very low dielectric absorption
- According to RoHS 2011/65/EC

### Typical Applications

For high frequency applications e.g.

- Sample and hold
- Timing
- LC-Filtering
- Oscillating circuits
- Audio equipment

### Construction


#### Dielectric:

Polypropylene (PP) film

#### Capacitor electrodes:

Metal foil

#### Internal construction:



#### Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

#### Terminations:

Tinned wire.

#### Marking:

Colour: Red. Marking: Black.

Epoxy resin seal: Yellow

### Electrical Data

#### Capacitance range:

33 pF to 0.033  $\mu$ F (E12-values on request)

#### Rated voltages:

63 VDC, 100 VDC, 250 VDC, 400 VDC, 630 VDC, 800 VDC, 1000 VDC

#### Capacitance tolerances:

$\pm 10\%$ ,  $\pm 5\%$ ,  $\pm 2.5\%$  ( $\pm 2\%$ ,  $\pm 1.5\%$  or  $\pm 1\%$  available as precision capacitors subject to special enquiry)

#### Operating temperature range:

$-55^\circ\text{C}$  to  $+100^\circ\text{C}$

#### Test specifications:

In accordance with IEC 60384-13

#### Climatic test category:

55/100/56 in accordance with IEC

#### Insulation resistance at $+20^\circ\text{C}$ :

$\geq 5 \times 10^5 \text{ M}\Omega$

(mean value:  $1 \times 10^6 \text{ M}\Omega$ )

Measuring voltage:

$U_r = 63 \text{ V}$ ;  $U_{\text{test}} = 50 \text{ V/1 min.}$

$U_r \geq 100 \text{ V}$ ;  $U_{\text{test}} = 100 \text{ V/1 min.}$

#### Dissipation factors at $+20^\circ\text{C}$ : $\tan \delta$

at f	$C \leq 1000 \text{ pF}$	$1000 \text{ pF} < C \leq 4700 \text{ pF}$	$C > 4700 \text{ pF}$
1 kHz	$\leq 3 \times 10^{-4}$	$\leq 4 \times 10^{-4}$	$\leq 4 \times 10^{-4}$
10 kHz	$\leq 3 \times 10^{-4}$	$\leq 4 \times 10^{-4}$	$\leq 4 \times 10^{-4}$
100 kHz	$\leq 4 \times 10^{-4}$	$\leq 5 \times 10^{-4}$	-
1 MHz	$\leq 10 \times 10^{-4}$	-	-

**Test voltage:**  $2 U_r$ , 2 sec.

#### Maximum pulse rise time:

1000 V/ $\mu$ sec for pulses equal to the rated voltage

#### Dielectric absorption:

0.05%

#### Temperature coefficient:

$-200 \times 10^{-6}/^\circ\text{C}$  (typical)

#### Voltage derating:

A voltage derating factor of 1.35 % per K must be applied from  $+85^\circ\text{C}$  for DC voltages and from  $+75^\circ\text{C}$  for AC voltages

#### Reliability:

Operational life  $> 300\,000$  hours

Failure rate  $< 5 \text{ fit}$  ( $0.5 \times U_r$  and  $40^\circ\text{C}$ )

### Mechanical Tests

#### Pull test on pins:

10 N in direction of pins according to IEC 60068-2-21

#### Vibration:

6 hours at 10...2000 Hz and 0.75 mm displacement amplitude or 10 g in accordance with IEC 60068-2-6

#### Low air density:

1kPa = 10 mbar in accordance with IEC 60068-2-13

#### Bump test:

4000 bumps at 390 m/sec<sup>2</sup> in accordance with IEC 60068-2-29

### Packing

Available taped and reeled.

Detailed taping information and graphs at the end of the catalogue.

For further details and graphs please refer to Technical Information.

## Continuation

### General Data

Capacitance	63 VDC/40 VAC*					100 VDC/63 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF	4.5	6	7.2	5	FKP2C001001D00_____	4.5	6	7.2	5	FKP2D001001D00_____
150 "	4.5	6	7.2	5	FKP2C001501D00_____	4.5	6	7.2	5	FKP2D001501D00_____
220 "	4.5	6	7.2	5	FKP2C002201D00_____	4.5	6	7.2	5	FKP2D002201D00_____
330 "	4.5	6	7.2	5	FKP2C003301D00_____	4.5	6	7.2	5	FKP2D003301D00_____
470 "	4.5	6	7.2	5	FKP2C004701D00_____	4.5	6	7.2	5	FKP2D004701D00_____
680 "	4.5	6	7.2	5	FKP2C006801D00_____	4.5	6	7.2	5	FKP2D006801D00_____
1000 pF	4.5	6	7.2	5	FKP2C011001D00_____	4.5	6	7.2	5	FKP2D011001D00_____
1500 "	4.5	6	7.2	5	FKP2C011501D00_____	4.5	6	7.2	5	FKP2D011501D00_____
2200 "	4.5	6	7.2	5	FKP2C012201D00_____	4.5	6	7.2	5	FKP2D012201D00_____
3300 "	4.5	6	7.2	5	FKP2C013301D00_____	5.5	7	7.2	5	FKP2D013301G00_____
4700 "	4.5	6	7.2	5	FKP2C014701D00_____	5.5	7	7.2	5	FKP2D014701G00_____
6800 "	4.5	6	7.2	5	FKP2C016801D00_____	5.5	7	7.2	5	FKP2D016801G00_____
0.01 µF	5.5	7	7.2	5	FKP2C021001G00_____	6.5	8	7.2	5	FKP2D021001I00_____
0.015 "	6.5	8	7.2	5	FKP2C021501I00_____	7.2	8.5	7.2	5	FKP2D021501J00_____
0.022 "	7.2	8.5	7.2	5	FKP2C022201J00_____	8.5	10	7.2	5	FKP2D022201L00_____
0.033 "	8.5	10	7.2	5	FKP2C023301L00_____					


Capacitance	250 VDC/160 VAC*					400 VDC/220 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF	4.5	6	7.2	5	FKP2F001001D00_____	4.5	6	7.2	5	FKP2G001001D00_____
150 "	4.5	6	7.2	5	FKP2F001501D00_____	4.5	6	7.2	5	FKP2G001501D00_____
220 "	4.5	6	7.2	5	FKP2F002201D00_____	4.5	6	7.2	5	FKP2G002201D00_____
330 "	4.5	6	7.2	5	FKP2F003301D00_____	4.5	6	7.2	5	FKP2G003301D00_____
470 "	4.5	6	7.2	5	FKP2F004701D00_____	4.5	6	7.2	5	FKP2G004701D00_____
680 "	4.5	6	7.2	5	FKP2F006801D00_____	4.5	6	7.2	5	FKP2G006801D00_____
1000 pF	4.5	6	7.2	5	FKP2F011001D00_____	4.5	6	7.2	5	FKP2G011001D00_____
1500 "	4.5	6	7.2	5	FKP2F011501D00_____	4.5	6	7.2	5	FKP2G011501D00_____
2200 "	4.5	6	7.2	5	FKP2F012201D00_____	4.5	6	7.2	5	FKP2G012201D00_____
3300 "	5.5	7	7.2	5	FKP2F013301G00_____	5.5	7	7.2	5	FKP2G013301G00_____
4700 "	6.5	8	7.2	5	FKP2F014701I00_____	6.5	8	7.2	5	FKP2G014701I00_____
6800 "	6.5	8	7.2	5	FKP2F016801I00_____	7.2	8.5	7.2	5	FKP2G016801J00_____
0.01 µF	7.2	8.5	7.2	5	FKP2F021001J00_____	8.5	10	7.2	5	FKP2G021001L00_____
0.015 "	8.5	10	7.2	5	FKP2F021501L00_____					

\* AC voltage:  $f \leq 1000 \text{ Hz}$ ;  $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$


\*\* PCM = Printed circuit module = pin spacing.

E12 values and individual values available from 27 pF up on request.

Dims. in mm.



Part number completion:	
Tolerance:	10 % = K
	5 % = J
	2.5 % = H
	2 % = G
	1.5 % = F
	1 % = E
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 148.	



Impedance change with frequency (general guide).

Rights reserved to amend design data without prior notification.

Continuation page 32

## Continuation

### General Data

Capacitance	630 VDC/250 VAC*					800 VDC/250 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
100 pF	4.5	6	7.2	5	FKP2J001001D00_	4.5	6	7.2	5	FKP2L001001D00_
150 "	4.5	6	7.2	5	FKP2J001501D00_	4.5	6	7.2	5	FKP2L001501D00_
220 "	4.5	6	7.2	5	FKP2J002201D00_	4.5	6	7.2	5	FKP2L002201D00_
330 "	4.5	6	7.2	5	FKP2J003301D00_	4.5	6	7.2	5	FKP2L003301D00_
470 "	4.5	6	7.2	5	FKP2J004701D00_	5.5	7	7.2	5	FKP2L004701G00_
680 "	4.5	6	7.2	5	FKP2J006801D00_	5.5	7	7.2	5	FKP2L006801G00_
1000 pF	4.5	6	7.2	5	FKP2J011001D00_	5.5	7	7.2	5	FKP2L011001G00_
1500 "	4.5	6	7.2	5	FKP2J011501D00_	5.5	7	7.2	5	FKP2L011501G00_
2200 "	5.5	7	7.2	5	FKP2J012201G00_	6.5	8	7.2	5	FKP2L012201I00_
3300 "	6.5	8	7.2	5	FKP2J013301I00_	7.2	8.5	7.2	5	FKP2L013301J00_
4700 "	6.5	8	7.2	5	FKP2J014701I00_	8.5	10	7.2	5	FKP2L014701L00_
6800 "	7.2	8.5	7.2	5	FKP2J016801J00_					
0.01 µF	8.5	10	7.2	5	FKP2J021001L00_					

Capacitance	1000 VDC/250 VAC*				
	W	H	L	PCM**	Part number
33 pF	4.5	6	7.2	5	FKP2O100331D00_
47 "	4.5	6	7.2	5	FKP2O100471D00_
68 "	4.5	6	7.2	5	FKP2O100681D00_
100 pF	4.5	6	7.2	5	FKP2O101001D00_
150 "	4.5	6	7.2	5	FKP2O101501D00_
220 "	4.5	6	7.2	5	FKP2O102201D00_
330 "	4.5	6	7.2	5	FKP2O103301D00_
470 "	5.5	7	7.2	5	FKP2O104701G00_
680 "	5.5	7	7.2	5	FKP2O106801G00_
1000 pF	6.5	8	7.2	5	FKP2O111001I00_
1500 "	7.2	8.5	7.2	5	FKP2O111501J00_
2200 "	8.5	10	7.2	5	FKP2O112201L00_

E12 values and individual values available from 27 pF up on request.

Dims. in mm.


Part number completion:	
Tolerance:	10 % = K
	5 % = J
	2.5 % = H
	2 % = G
	1.5 % = F
	1 % = E
Packing:	bulk = S
Pin length:	6-2 = SD
Taped version see page 148.	

\* AC voltage:  $f \leq 1000 \text{ Hz}$ ;  $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

\*\* PCM = Printed circuit module = pin spacing.

Rights reserved to amend design data without prior notification.

Permissible AC voltage in relation to frequency at 10° C internal temperature rise (general guide).



## Recommendation for Processing and Application of Through-Hole Capacitors

### Soldering Process

A preheating of through-hole WIMA capacitors is allowed for temperatures  $T_{\max} < 100^{\circ}\text{C}$ .  
In practice a preheating duration of  $t < 5$  min. has been proven to be best.


#### Single wave soldering

Soldering bath temperature:  $T < 260^{\circ}\text{C}$   
Immersion time:  $t < 5$  sec

#### Double wave soldering

Soldering bath temperature:  $T < 260^{\circ}\text{C}$   
Immersion time:  $2 \times t < 3$  sec

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



## WIMA Quality and Environmental Philosophy

### ISO 9001:2008 Certification

ISO 9001:2008 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2008 of our factories by the VDE inspectorate certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

### WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application of WPCS during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- AQL check

### WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- Lead
- PCB
- CFC
- Hydrocarbon chloride
- Chromium 6+
- PBB/PBDE
- Arsenic
- Cadmium
- Mercury
- etc.

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- foamed polystyrene (Styropor®)
- adhesive tapes made of plastic
- metal clips

### RoHS Compliance

According to the RoHS Directive 2011/65/EC certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei  
konform RoHS 2011/65/EC  
WIMA capacitors are lead free  
in accordance with RoHS 2011/65/EC

Tape for lead-free WIMA capacitors

### DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

# Typical Dimensions for Taping Configuration




Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5\*mm

\*PCM 27.5 tapping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping										
		PCM 2.5 tapping	PCM 5 tapping	PCM 7.5 tapping	PCM 10 tapping*	PCM 15 tapping*	PCM 22.5 tapping	PCM 27.5 tapping				
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5				
Hold-down tape width	W <sub>0</sub>	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape				
Hole position	W <sub>1</sub>	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5				
Hold-down tape position	W <sub>2</sub>	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.				
Feed hole diameter	D <sub>0</sub>	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2				
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5				
Feed hole pitch	P <sub>0</sub>	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch				
Feed hole centre to pin	P <sub>1</sub>	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7				
Hole centre to component centre	P <sub>2</sub>	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3				
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5				
Feed hole centre to top edge of the component	H <sub>1</sub>	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 32.25 max.	H+H <sub>component</sub> < H <sub>1</sub> 24.5 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 25.0 to 31.5	H+H <sub>component</sub> < H <sub>1</sub> 26.0 to 37.0	H+H <sub>component</sub> < H <sub>1</sub> 30.0 to 43.0	H+H <sub>component</sub> < H <sub>1</sub> 35.0 to 45.0				
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 <sup>+0.8</sup> <sub>-0.2</sub>	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8				
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.5 ±0.05 or 0.6 <sup>+0.06</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>	0.8 <sup>+0.08</sup> <sub>-0.05</sub>				
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.				
Total tape thickness	t	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2	0.7 ±0.2				
Package (see also page 149)	ROLL/AMMO			AMMO								
	REEL	φ 360 max. φ 30 ±1	B 52 ±2 58 ±2	depending on comp. dimensions		REEL	φ 360 max. φ 30 ±1	B 52 ±2 58 ±2 or 66 ±2	REEL	φ 500 max. φ 25 ±1	B 60 ±2 68 ±2	depending on PCM and component dimensions
Unit	see details page 150.											

Dims in mm.

\* Diameter of pins see General Data.


\* PCM 10 and PCM 15 can be crimped to PCM 7.5.

Position of components according to PCM 7.5 (sketch 11). P<sub>0</sub> = 12.7 or 15.0 is possible


Please clarify customer-specific deviations with the manufacturer.

## Types of Tape Packaging of Capacitors for Automatic Radial Insertion


### ■ ROLL Packaging



### ■ AMMO Packaging



### ■ REEL Packaging



## BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumerical Bar Code

Scanner decoding of

- WIMA supplier number
- Customer's P/O number
- Customer's part number
- WIMA confirmation number
- WIMA part number
- Lot number
- Date code
- Quantity

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- capacitance tolerance
- packing

as well as gross weight and customer's name are indicated in plain text.

<b>WIMA</b> Best Capacitors Made in Germany		Werk Unna	
Supplier-ID: 123456789	<b>RoHS</b> 2011/65/EC	Date Code: 08.10.10	
Purchase Order No. (P/O): Bestellung xyz		Quantity: 5.000	
Customer Part No.: KUNDETEILENUMMER		Customer No.: 0000100002	
		Gross Weight [g]: 1870	
WIMA Confirmation No.: 0001004053000100	WIMA Part No.: MKS2C034701C00K88D		
Handling Unit: <b>MKS 2</b>	<b>QTY: 5.000</b>	<b>COO: DE</b>	
	<b>MKS 2 0.47 µF 63 VDC 3.5x8.5x7.2 RMS</b>		
<b>1000067326</b>	Standard 10% Loss - Standard	Drühte 6-2	Week 03/2011
	Vorlage Debitor Inland		

BARCODE „Code 39“



## Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm

PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
	W	H	L	Codes		S	H16.5	H18.5	ø 360	ø 500	340 × 340	490 × 370			
					N	O	F	I	H	J	A	C	B	D	
<b>2.5 mm</b>	2.5	7	4.6	<b>0B</b>	5000		2200	2500				2800			
	3	7.5	4.6	<b>0C</b>	5000		2000	2300				2300			
	3.8	8.5	4.6	<b>0D</b>	5000		1500	1800				1800			
	4.6	9	4.6	<b>0E</b>	5000		1200	1500				1500			
	5.5	10	4.6	<b>0F</b>	5000		900	1200				1200			
<b>5 mm</b>	2.5	6.5	7.2	<b>1A</b>	5000		2200	2500				2800			
	3	7.5	7.2	<b>1B</b>	5000		2000	2300				2300			
	3.5	8.5	7.2	<b>1C</b>	5000		1600	2000				2000			
	4.5	6	7.2	<b>1D</b>	6000		1300	1500				1500			
	4.5	9.5	7.2	<b>1E</b>	4000		1300	1500				1500			
	5	10	7.2	<b>1F</b>	3500		1100	1400				1400			
	5.5	7	7.2	<b>1G</b>	4000		1000	1200				1200			
	5.5	11.5	7.2	<b>1H</b>	2500		1000	1200				1200			
	6.5	8	7.2	<b>1I</b>	2500		800	1000				1000			
	7.2	8.5	7.2	<b>1J</b>	2500		700	1000				1000			
	7.2	13	7.2	<b>1K</b>	2000		700	950				1000			
	8.5	10	7.2	<b>1L</b>	2000		600	800				800			
	8.5	14	7.2	<b>1M</b>	1500		600	800				800			
11	16	7.2	<b>1N</b>	1000		500	600				400				
<b>7.5 mm</b>	2.5	7	10	<b>2A</b>	5000			2500	4400		2500				
	3	8.5	10	<b>2B</b>	5000			2200	4300		2300			4150	
	4	9	10	<b>2C</b>	4000			1700	3200		1700			3100	
	4.5	9.5	10.3	<b>2D</b>	3500			1500	2900		1400			2800	
	5	10.5	10.3	<b>2E</b>	3000			1300	2500		1300				
	5.7	12.5	10.3	<b>2F</b>	2000			1000	2200		1100				
	7.2	12.5	10.3	<b>2G</b>	1500			900	1800		1000				
<b>10 mm</b>	3	9	13	<b>3A</b>	3000			1100	2200					1900	
	4	8.5	13.5	<b>FA</b>	3000			900	1600					1450	
	4	9	13	<b>3C</b>	3000			900	1600					1450	
	4	9.5	13	<b>3D</b>	3000			900	1600					1400	
	5	10	13.5	<b>FB</b>	2000			700	1300					1200	
	5	11	13	<b>3F</b>	3000			700	1300					1200	
	6	12	13	<b>3G</b>	2400			550	1100					1000	
	6	12.5	13	<b>3H</b>	2400			550	1100					1000	
8	12	13	<b>3I</b>	2000			400	800					740		
<b>15 mm</b>	5	11	18	<b>4B</b>	2400			600	1200					1150	
	5	13	19	<b>FC</b>	1000			600	1200					1200	
	6	12.5	18	<b>4C</b>	2000			500	1000					1000	
	6	14	19	<b>FD</b>	1000			500	1000					1000	
	7	14	18	<b>4D</b>	1600			450	900					850	
	7	15	19	<b>FE</b>	1000			450	900					850	
	8	15	18	<b>4F</b>	1200			400	800					740	
	8	17	19	<b>FF</b>	500			400	800					740	
	9	14	18	<b>4H</b>	1200			350	700					650	
	9	16	18	<b>4J</b>	900			350	700					650	
	10	18	19	<b>FG</b>	500			300	650					590	
11	14	18	<b>4M</b>	1000			300	600					540		
<b>22.5 mm</b>	5	14	26.5	<b>5A</b>	1200				800					770	
	6	15	26.5	<b>5B</b>	1000				700					640	
	7	16.5	26.5	<b>5D</b>	760				600					550	
	8	20	28	<b>FH</b>	500				500					480	
	8.5	18.5	26.5	<b>5F</b>	500				480					450	
	10	22	28	<b>FI</b>	540*				420					380	
	10.5	19	26.5	<b>5G</b>	680*				400					360	
	10.5	20.5	26.5	<b>5H</b>	680*				400					360	
	11	21	26.5	<b>5I</b>	680*				380					350	
	12	24	28	<b>FJ</b>	450*				350					310	

\* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.



## Packing Quantities for Capacitors with Radial Pins in PCM 27.5 mm to 52.5 mm

PCM	Size				bulk	pcs. per packing unit											
						ROLL		REEL				AMMO					
	W	H	L	Codes		S	N	O	ø 360		ø 500		340 x 340		490 x 370		
								H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5	H16.5	H18.5
								F	I	H	J	A	C	B	D		
<b>27.5 mm</b>	9	19	31.5	<b>6A</b>	640*	-	-	-	-	460/340*	-	-	420				
	11	21	31.5	<b>6B</b>	544*	-	-	-	-	380/280*	-	-	350				
	13	24	31.5	<b>6D</b>	448*	-	-	-	-	300	-	-	290				
	13	25	33	<b>6K</b>	336*	-	-	-	-	-	-	-	-				
	15	26	31.5	<b>6F</b>	384*	-	-	-	-	270	-	-	250				
	15	26	33	<b>6L</b>	288*	-	-	-	-	-	-	-	-				
	17	29	31.5	<b>6G</b>	176*	-	-	-	-	-	-	-	-				
	17	34.5	31.5	<b>6I</b>	176*	-	-	-	-	-	-	-	-				
	19	30	31.5	<b>6L</b>	50*	-	-	-	-	-	-	-	-				
	20	32	33	<b>6M</b>	216*	-	-	-	-	-	-	-	-				
20	39.5	31.5	<b>6J</b>	144*	-	-	-	-	-	-	-	-					
<b>37.5 mm</b>	9	19	41.5	<b>7A</b>	480*	-	-	-	-	-	-	-	-				
	11	22	41.5	<b>7B</b>	408*	-	-	-	-	-	-	-	-				
	13	24	41.5	<b>7C</b>	252*	-	-	-	-	-	-	-	-				
	15	26	41.5	<b>7D</b>	144*	-	-	-	-	-	-	-	-				
	17	29	41.5	<b>7E</b>	132*	-	-	-	-	-	-	-	-				
	19	32	41.5	<b>7F</b>	108*	-	-	-	-	-	-	-	-				
	20	39.5	41.5	<b>7G</b>	108*	-	-	-	-	-	-	-	-				
	24	45.5	41.5	<b>7H</b>	84*	-	-	-	-	-	-	-	-				
	31	46	41.5	<b>7I</b>	72*	-	-	-	-	-	-	-	-				
	35	50	41.5	<b>7J</b>	35*	-	-	-	-	-	-	-	-				
40	55	41.5	<b>7K</b>	28*	-	-	-	-	-	-	-	-					
<b>48.5 mm</b>	19	31	56	<b>8D</b>	50*	-	-	-	-	-	-	-	-				
	23	34	56	<b>8E</b>	72*	-	-	-	-	-	-	-	-				
	27	37.5	56	<b>8H</b>	60*	-	-	-	-	-	-	-	-				
	33	48	56	<b>8J</b>	48*	-	-	-	-	-	-	-	-				
	37	54	56	<b>8L</b>	25*	-	-	-	-	-	-	-	-				
<b>52.5 mm</b>	35	50	57	<b>9F</b>	25*	-	-	-	-	-	-	-	-				
	45	55	57	<b>9H</b>	20*	-	-	-	-	-	-	-	-				
	45	65	57	<b>9J</b>	20*	-	-	-	-	-	-	-	-				

\* for 2-inch transport pitches.

\* TPS (Tray-Packing-System). Plate versions may have different packing units. Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.





# WIMA Part Number System

A WIMA part number consists of 18 digits and is composed as follows:

- Field 1 - 4: Type description
- Field 5 - 6: Rated voltage
- Field 7 - 10: Capacitance
- Field 11 - 12: Size and PCM
- Field 13 - 14: Version code (e.g. Snubber versions)
- Field 15: Capacitance tolerance
- Field 16: Packing
- Field 17 - 18: Lead length (untaped)

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
<b>M</b>	<b>K</b>	<b>S</b>	<b>2</b>	<b>C</b>	<b>0</b>	<b>2</b>	<b>1</b>	<b>0</b>	<b>0</b>	<b>1</b>	<b>A</b>	<b>0</b>	<b>0</b>	<b>M</b>	<b>S</b>	<b>S</b>	<b>D</b>
MKS 2				63 VDC		0.01 µF			2.5x6.5x7.2		-		20%	bulk	6-2		

<p><b>Type description:</b></p> <p>SMD-PET = SMDT  SMD-PPS = SMDI  FKP 02 = FKP0  MKS 02 = MKS0  FKS 2 = FKS2  FKP 2 = FKP2  MKS 2 = MKS2  MKS 2 = MKP2  FKS 3 = FKS3  FKP 3 = FKP3  MKS 4 = MKS4  MKP 4 = MKP4  MKP 10 = MKP1  FKP 4 = FKP4  FKP 1 = FKP1  MKP-X2 = MKX2  MKP-X2 R = MKXR  MKP-Y2 = MKY2  MP 3-X2 = MPX2  MP 3-X1 = MPX1  MP 3-Y2 = MPY2  MP 3R-Y2 = MPRY  Snubber MKP = SNMP  Snubber FKP = SNFP  GTO MKP = GTOM  DC-LINK MKP 3 = DCP3  DC-LINK MKP 4 = DCP4  DC-LINK MKP 4S = DCPS  DC-LINK MKP 5 = DCP5  DC-LINK MKP 6 = DCP6  DC-LINK HC = DCH_  DC-LINK HY = DCHY  SuperCap C = SCSC  SuperCap MC = MC_  SuperCap C60 = SCSC  SuperCap R = SCSR  SuperCap MR = MRPP</p>	<p><b>Rated voltage:</b></p> <p>2.5 VDC = A1  4 VDC = A2  14 VDC = A3  28 VDC = A4  40 VDC = A5  5 VDC = A6  50 VDC = B0  63 VDC = C0  100 VDC = D0  160 VDC = E0  250 VDC = F0  400 VDC = G0  450 VDC = H0  600 VDC = I0  630 VDC = J0  700 VDC = K0  800 VDC = L0  850 VDC = M0  900 VDC = N0  1000 VDC = O1  1100 VDC = P0  1200 VDC = Q0  1250 VDC = R0  1500 VDC = S0  1600 VDC = T0  2000 VDC = U0  2500 VDC = V0  3000 VDC = W0  4000 VDC = X0  6000 VDC = Y0  250 VAC = 0W  275 VAC = 1W  300 VAC = 2W  400 VAC = 3W  440 VAC = 4W  500 VAC = 5W  ...</p>	<p><b>Capacitance:</b></p> <p>22 pF = 0022  47 pF = 0047  100 pF = 0100  150 pF = 0150  220 pF = 0220  330 pF = 0330  470 pF = 0470  680 pF = 0680  1000 pF = 1100  1500 pF = 1150  2200 pF = 1220  3300 pF = 1330  4700 pF = 1470  6800 pF = 1680  0.01 µF = 2100  0.022 µF = 2220  0.047 µF = 2470  0.1 µF = 3100  0.22 µF = 3220  0.47 µF = 3470  1 µF = 4100  2.2 µF = 4220  4.7 µF = 4470  10 µF = 5100  22 µF = 5220  47 µF = 5470  100 µF = 6100  220 µF = 6220  1 F = A010  2.5 F = A025  50 F = A500  100 F = B100  110 F = B110  600 F = B600  1200 F = C120  ...</p>	<p><b>Size:</b></p> <p>4.8x3.3x3 Size 1812 = KA  4.8x3.3x4 Size 1812 = KB  5.7x5.1x3.5 Size 2220 = QA  5.7x5.1x4.5 Size 2220 = QB  7.2x6.1x3 Size 2824 = TA  7.2x6.1x5 Size 2824 = TB  10.2x7.6x5 Size 4030 = VA  12.7x10.2x6 Size 5040 = XA  15.3x13.7x7 Size 6054 = YA  2.5x7x4.6 PCM 2.5 = 0B  3x7.5x4.6 PCM 2.5 = 0C  2.5x6.5x7.2 PCM 5 = 1A  3x7.5x7.2 PCM 5 = 1B  2.5x7x10 PCM 7.5 = 2A  3x8.5x10 PCM 7.5 = 2B  3x9x13 PCM 10 = 3A  4x9x13 PCM 10 = 3C  5x11x18 PCM 15 = 4B  6x12.5x18 PCM 15 = 4C  5x14x26.5 PCM 22.5 = 5A  6x15x26.5 PCM 22.5 = 5B  9x19x31.5 PCM 27.5 = 6A  11x21x31.5 PCM 27.5 = 6B  9x19x41.5 PCM 37.5 = 7A  11x22x41.5 PCM 37.5 = 7B  94x49x182 DCH_ = H0  94x77x182 DCH_ = H1  ...</p> <p><b>Version code:</b></p> <p>Standard = 00  Version A1 = 1A  Version A1.1.1 = 1B  Version A2 = 2A  ...</p>	<p><b>Tolerance:</b></p> <p>20% = M  10% = K  5% = J  2.5% = H  1% = E  ...</p> <p><b>Packing:</b></p> <p>AMMO H16.5 340x340 = A  AMMO H16.5 490x370 = B  AMMO H18.5 340x340 = C  AMMO H18.5 490x370 = D  REEL H16.5 360 = F  REEL H16.5 500 = H  REEL H18.5 360 = I  REEL H18.5 500 = J  ROLL H16.5 = N  ROLL H18.5 = O  BLISTER W12 180 = P  BLISTER W12 330 = Q  BLISTER W16 330 = R  BLISTER W24 330 = T  Bulk/TPS Standard = S  ...</p> <p><b>Lead length (untaped)</b></p> <p>3.5 ±0.5 = C9  6-2 = SD  16 ±1 = P1  ...</p>
---	---	---	--	--

The data on this page is not complete and serves only to explain the part number system. Part number information is listed on the pages of the respective WIMA range.