

LAN cable


FABER[®] dataline 1000 STP (S-FTP)



Application: For the connection of IT system units in the desktop area (tertiary sector), e.g. between floor distributors and workstation up to 1000 Mbit/s (category 7+). It fully complies with the electromagnetic compatibility requirements (EMC) of European Standard EN 55022 and the guidelines of the European Postal Administration. Furthermore, the copper braiding ensures perfect matching with screened connectors.

Construction and technical data:

CPR-classification according to EN 50575:	Dca
Specification/Standard:	ISO/IEC 11801, EN 50173, EN 55022, EN 50288-4-1, EN 50167, EN 50169
Conductor material:	copper, bare
Insulation:	foam-PE
Screen over strand:	tinned copper braid
Screen over stranding unit:	Foil
Sheathing material:	FRNC-compound HM2
Colour of outer sheath:	orange RAL 2004
Flame-retardant:	VDE 0482-332-1-2/IEC 60332-1-2
Smoke density:	DIN EN 61034/IEC 61034
Halogen-free:	DIN EN 50267/IEC 60754
Permitted outer cable temperature, fixed, °C:	-20 - +70 °C
Permitted outer cable temperature, moved, °C:	0 - 50 °C
Bending radius, fixed installation:	4 x Ø
Bending radius, moving application:	8 x Ø
Impedance:	100 Ohm
Transfer impedance:	5 Ohm/km
Velocity factor (NVP):	0.78 v/c
Category:	7+
Segregation class (EN 50174-2):	d
Power over Ethernet (PoE):	PoE+/IEEE 802.3at Type 2



The products and information presented here are for technical calculation only. They are subject to technical progress and in no way represent the ability of shipment. Outer diameters are approximately.

HF-Parameter

f, MHz	attenuation, nominal value, n dB/100 m	attenuation, typical value, dB/100 m	NEXT, dB, nominal value	NEXT, dB, typical value	PS-NEXT, dB, typical value	ELFEXT, dB/100 m, typical value	PS-EL-FEXT, dB/100 m, typical value	PS-ACR, dB, typical value	Return loss, dB, typical value
1	2	1.9	80	100	97	90	87	95.1	27
10	5.7	5.5	80	100	97	90	87	95.1	30
16	7.2	6.9	80	100	97	86.7	83.7	90	30
20	8.1	7.8	80	100	97	84.8	81.8	89.2	30
100	18.8	18	72	94	91.3	70.8	67.8	73.3	25.1
155	23.4	22.7	70	91	87.9	67	64	65.1	23.8
300	33.3	32.5	65	85	82.7	61.3	58.3	50.3	21.8
600	48.9	47.6	61	80	77.3	55.2	52.2	29.6	19.7
900	-	60.0	-	77	74.1	51.7	48.7	14.1	18.4
1000	-	63.8	-	76	73.3	50.8	47.8	9.5	18.1

FABER[®] dataline 1000

Maximum operating capacity:	56 nF/km
Test voltage:	2.5 kV
Core identification:	colours acc. to IEC 60708

part no.	part name	DI [mm]	RI [Ohm/km]	Ø [mm]	Ev [kWh/m]	Fzv [N]	Cu	G [kg]
100952	Faber [®] dataline 1000 STP 4X2X AWG 23 PiMF FRNC OR	0.56	75	7.5	0.19	98	32	52
101043	Faber [®] dataline 1000 STP 4X2X AWG 23 PiMF FRNC OR Reel in Box 200 m	0.56	75	7.5	0.19	98	32	52
101318	Faber [®] dataline 1000 STP 4X2X AWG 23 PiMF FRNC OG 100 m coil	0.56	75	7.5	0.19		32	52

FABER[®] dataline 1000 duplex

Maximum operating capacity:	56 nF/km
Test voltage:	2.5 kV
Core identification:	colours acc. to IEC 60708

part no.	part name	DI [mm]	RI [Ohm/km]	w [mm]	h [mm]	Ev [kWh/m]	Fzv [N]	Cu	G [kg]
100951	Faber [®] dataline 1000 Duplex STP 2X4X2X AWG 23 PiMF FRNC OR	0.56	75	15.2	7.5	0.39	196	64	104
101196	Faber [®] dataline 1000 Duplex STP 2X4X2X AWG 23 PiMF FRNC OR Reel in Box 100 m	0.56	75	15.2	7.5	0.39	196	64	104

DI	diameter conductor
RI	Conductor resistance
w	Width of (flat) cable approx.
h	Approx. height of (flat) cable
Ø	outer diameter approx.
Ev	Combustion heat (fire load)
Fzv	Tensile strength (during installation)
Cu	Copper weight (GER)
G	net weight per 1000