

For Automotive Chip Ferrite Bead for Automotive

BLM21B Series (0805 Size)

Dimensions



■ Equivalent Circuit



Packaging

Code	Packaging	Minimum Quantity	
D	180mm Paper Tape	4000	
J	330mm Paper Tape	10000	
В	Bulk(Bag)	1000	

• Only applied to BLM21BD222SH1/21BD272SH1

Code	Packaging	Minimum Quantity	
L	180mm Plastic Tape	3000	
K	330mm Plastic Tape	10000	
В	Bulk(Bag)	1000	

■ Rated Value (□: packaging code)

Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range
BLM21BD121SH1□	120ohm ±25%	-	200mA	0.25ohm max.	-55 to +125°C
BLM21BD151SH1□	150ohm ±25%	-	200mA	0.25ohm max.	-55 to +125°C
BLM21BD221SH1□	220ohm ±25%	-	200mA	0.25ohm max.	-55 to +125°C
BLM21BD331SH1□	330ohm ±25%	-	200mA	0.30ohm max.	-55 to +125°C
BLM21BD421SH1□	420ohm ±25%	-	200mA	0.30ohm max.	-55 to +125°C
BLM21BD471SH1□	470ohm ±25%	-	200mA	0.35ohm max.	-55 to +125°C
BLM21BD601SH1□	600ohm ±25%	-	200mA	0.35ohm max.	-55 to +125°C
BLM21BD751SH1□	750ohm ±25%	-	200mA	0.40ohm max.	-55 to +125°C
BLM21BD102SH1□	1000ohm ±25%	-	200mA	0.40ohm max.	-55 to +125°C
BLM21BD152SH1□	1500ohm ±25%	-	200mA	0.45ohm max.	-55 to +125°C
BLM21BD182SH1□	1800ohm ±25%	-	200mA	0.50ohm max.	-55 to +125°C
BLM21BD222TH1□	2200ohm ±25%	-	200mA	0.60ohm max.	-55 to +125°C
BLM21BD222SH1□	2250ohm (Typ.)	-	200mA	0.60ohm max.	-55 to +125°C
BLM21BD272SH1□	2700ohm ±25%	-	200mA	0.80ohm max.	-55 to +125°C
BLM21BB050SH1□	5ohm ±25%	-	1000mA	0.02ohm max.	-55 to +125°C
BLM21BB600SH1□	60ohm ±25%	-	800mA	0.13ohm max.	-55 to +125°C
BLM21BB750SH1□	75ohm ±25%	-	700mA	0.16ohm max.	-55 to +125°C
BLM21BB121SH1□	120ohm ±25%	-	600mA	0.19ohm max.	-55 to +125°C
BLM21BB151SH1□	150ohm ±25%	-	600mA	0.21ohm max.	-55 to +125°C
BLM21BB201SH1□	200ohm ±25%	-	500mA	0.26ohm max.	-55 to +125°C

Number of Circuits: 1

Continued on the following page.




- 1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.


Part Number	Impedance (at 100MHz/20°C)	Impedance (at 1GHz/20°C)	Rated Current	DC Resistance	Operating Temperature Range
BLM21BB221SH1□	220ohm ±25%	-	500mA	0.26ohm max.	-55 to +125°C
BLM21BB331SH1□	330ohm ±25%	-	400mA	0.33ohm max.	-55 to +125°C
BLM21BB471SH1□	470ohm ±25%	-	400mA	0.4ohm max.	-55 to +125°C

Number of Circuits: 1


■ Impedance-Frequency Characteristics (Main Items) **BLM21BD Series**




■ Impedance-Frequency Characteristics (Main Items) **BLM21BB Series**



■ Impedance-Frequency Characteristics BLM21BD121SH1



■ Impedance-Frequency Characteristics BLM21BD151SH1




Continued on the following page.


- 1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.


■ Impedance-Frequency Characteristics BLM21BD221SH1




■ Impedance-Frequency Characteristics BLM21BD331SH1




■ Impedance-Frequency Characteristics BLM21BD421SH1




■ Impedance-Frequency Characteristics BLM21BD471SH1



■ Impedance-Frequency Characteristics BLM21BD601SH1



■ Impedance-Frequency Characteristics BLM21BD751SH1



Continued on the following page.




3


- 1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.


■ Impedance-Frequency Characteristics BLM21BD102SH1




■ Impedance-Frequency Characteristics BLM21BD152SH1




■ Impedance-Frequency Characteristics BLM21BD182SH1




■ Impedance-Frequency Characteristics BLM21BD222TH1



■ Impedance-Frequency Characteristics BLM21BD222SH1



■ Impedance-Frequency Characteristics BLM21BD272SH1




Continued on the following page.




- 1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.


■ Impedance-Frequency Characteristics BLM21BB050SH1




■ Impedance-Frequency Characteristics BLM21BB600SH1




■ Impedance-Frequency Characteristics BLM21BB750SH1




■ Impedance-Frequency Characteristics BLM21BB121SH1



■ Impedance-Frequency Characteristics BLM21BB151SH1



■ Impedance-Frequency Characteristics **BLM21BB201SH1**



Continued on the following page.




5


- 1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.

Continued from the preceding page.

■ Impedance-Frequency Characteristics BLM21BB221SH1




■ Impedance-Frequency Characteristics BLM21BB331SH1



6

■ Impedance-Frequency Characteristics BLM21BB471SH1



■ ⚠ Caution/Notice

- 1. Do not use products beyond the rated current as this may create excessive heat and deteriorate the insulation resistance.
- 2. Be sure to provide an appropriate fail-safe function on your product to prevent a second damage that may be caused by the abnormal function or the failure our product.

Notice

Solderability of Tin plating termination chip might be deteriorated when low temperature soldering profile where peak solder temperature is below the Tin melting point is used. Please confirm the solderability of Tin plating termination chip before use.

- 1. This datasheet is downloaded from the website of Murata Manufacturing co., ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.