






**Φ22 mm, rocker switch, 2 position, 2NO,
BN no. 1303043**

Version 01/15



Contact Composition

(The switch code is 20; 1,2,3,4
are all normal opened(NO).)

Install instruction

Specification	LAS0-K-20C21
Mounting diameter	22 mm
Switching voltage	250 V/AC
Switching current	5 A
Connection	screw terminal
Contact resistance	$\leq 50 \text{ m}\Omega$

Insulation resistance	$\geq 100 \text{ M}\Omega$
Dielectric intensity	2000 V/AC
Operating and storage temperature	-20 to +70 °C
Operating and storage humidity	45 to 85 % RH
Panel thickness	0.5 ~ 5 mm
Electrical lifespan	50,000 cycles
Durability	500,000 cycles
Base	PA



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2015 by Conrad Electronic SE.