



SIM CARD PINOUT		
PIN NO.	NAME	DESCRIPTION
C1	VCC	+5V OR 3.3V DC
C2	RST	CARD RESET (OPTIONAL)
C3	CLK	CARD CLOCK
C5	GND	GROUND
C6	VPP	+21V DC
C7	I/O	IN/OUT

### MATERIALS

- HOUSING : HI.-TEMP.PLASTIC(UL 94V-0).BLACK
- TERMINAL : COPPER ALLOY.(t=0.15mm)  
GOLD PLATED OVER NICKEL
- FORK : COPPER ALLOY. (t=0.20mm)  
TIN PLATED OVER NICKEL


### SPECIFICATION

- CURRENT RATING : 1.0 A MAX.
- DIELECTRIC WITHSTANDING VOLTAGE :  
500V AC R.M.S. FOR ONE MINUTE.
- INSULATION RESISTANCE : 1000MΩ MIN. AT 500V DC.
- CONTACT RESISTANCE : 30mΩ MAX.
- OPERATING TEMPERATURE : -40°C TO +85°C.




PRODUCT NUMBER:  
115C-A C 0 0-R  
1 2 3

- Type  
A:6Pin
- Contact Plating  
C:Gold Flash
- RoHS



REV.	DESCRIPTION	DATE	REV.	DESCRIPTION	DATE	SIZE	REV.	FILE NAME
1			4			A4	1.0	115C-AC00-R_B_2
2			5					
3			6					

UNLESS OTHERWISE SPECIFIED TOLERANCE			 www.attend.com.tw	
ANGLES	ANG.	±5°		
LINEAR	0.	±0.3		
	0.0	±0.25		
	0.00	±0.20		
SCALE	AS SHOWN	UNIT: mm		
DRAWN	Willis	2012/08/03	DRAWN NAME: SIM Card Socket With Card Holder	
CHECKED	Angel	2012/08/03	PRODUCT NO.	115C-AC00-R
APPROVED	Ken	2012/08/03	FILE NAME	115C-AC00-R_B_2

- Revise:
- Revise:
- Revise: