




+ 44 (0) 208 920 2306 www.energizer-eu.com

SILVER OXIDE

## ENERGIZER 321





Chemical System:


ZEROMERCURY

Nominal Voltage: Typical Capacity: Capacity Test: Typical Weight: Typical Volume: Impedance (40 Hz): 1.55 Volts
15 mAh\* (to 1.2 volts)
100K ohm continuous drain at 21°C
0.28 grams (0.01 oz.)
0.07 cubic centimeters (0.004 cubic inch)
30 to 40 ohms

**Specifications** 

Silver Oxide (Zn/Ag<sub>2</sub>O)


\* Varies according to the applied load, temperature, and cutoff voltage.



DESIGNED FOR USE ON CONTINUOUS LOW DRAIN


## **Typical Discharge Characteristics**

Typical Performance at 21°C (70°F)



## **Temperature Characteristics**

Typical Performance at Low Discharge Rates



## **Important Notice**

This datasheet contains typical information specific to products manufactured at the time of its publication. ©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.