



Reference: 10084





1. General description

Maintains and protects all electrical equipment. Displaces and seals out water and moisture. Prevents corrosion and oxidation. Penetrates and lubricates.



2. Features

- Multi purpose fluid.
- Does not contain silicones.
- Protects metals and alloys.
- Displaces and seals out water and moisture.
- Loosens metal parts seized by dirt, corrosion or dried-up grease.
- Penetrates quickly.
- Safe on all metal surfaces, does not stain.
- Safe on most rubbers, plastics and coatings. Test on sensitive or stressed materials before use.
- Convenient 360° (including inverted position) spray valve for aerosols.
- High purity CO2 propellant, giving an active product content of 95%.

3. Applications

• Electro-mechanical assemblies.



Manufactured by:

CRC Industries Europe byba

Touwslagerstraat 1 9240 Zele Belgium Tél.: (32)(0) 52/45.60.11 Fax : (32)(0) 52/45.00.34

www.crcind.com





Reference: 10084

- Control assemblies.
- Electrical aggregates.
- All electrical contacts.
- Printed circuit boards.
- Coin mechanisms.
- Fine mechanics.

4. Directions

- For lubrication and protection: spray a light even coat.
- To remove moisture: spray liberally and allow to drip off.
- When applied by dipping, agitation accelerates the action.
- Test before use on sensitive materials.
- Do not use on energized equipment.
- Do not use on sensitive electronic equipment.
- Allow to dry completely before reactivation.
- To remove residues or excess product, use one of the CRC cleaners.
- \bullet A safety data sheet (MSDS) according to EC Regulation N° 1907/2006 Art.31 and amendments is available for all CRC products.

Aerosol

5. Typical product data (without propellant)

Appearance	Liquid.	Liquid.
Color	Amber.	Amber.
Odor	Salicylate.	Salicylate.
Density	0.83 g/cm3 (@ 20°C).	0.83 g/cm3 (@ 20°C).
Flash Point	75 °C (Closed Cup)	75 °C (Closed Cup)
Viscosity	4 mPa.s (@ 20°C).	4 mPa.s (@ 20°C).
Density active product	0.89 g/cm3 (@ 20°C).	0.89 g/cm3 (@ 20°C).
4-ball weld load active product	8900 N	8900 N
Operating temperature active product	max 120 °C	max 120 °C
salt spray resistance active product	55 h	55 h
Typical coat weight	2 μm	2 μm



Manufactured by:

CRC Industries Europe byba

Touwslagerstraat 1 9240 Zele Belgium Tél.: (32)(0) 52/45.60.11 Fax : (32)(0) 52/45.00.34

www.crcind.com



Bulk



Reference: 10084

6. Packaging

Aerosol 12x200 ML

12x400 ML 12x500 ML 24x200 ML

Bulk 20 L

200 L 2x5 L 6x1 L

7. Remarks

Typical corrosion protection results will depend mainly on surface conditions and indoor environment. It may be less than 1 month or more than 6 months. The first application should be checked periodically for signs of corrosion. Once the time of protection under any specific condition is determined, CRC 2-26 may be re-applied at intervals to maintain protection.

All statements in this publication are based on service experience and/or laboratory testing. Because of the wide variety of equipment, conditions of use and the unpredictable human factors involved, we recommend that our products are tested on-the-job prior to use. All information is given in good faith but without warranty neither expressed nor implied. This Technical Data Sheet may already have been revised as a result of a change in legislation, availability of components or newly acquired experiences. The latest and only valid version of this Technical Data Sheet will be sent to you upon simple request or can be found on our website: www.crcind.com We recommend that you register on our website for this product, thus enabling you to automatically receive any future updates.

Version CRC_GREEN-2_26-20130604

Date



Manufactured by:

CRC Industries Europe byba

Touwslagerstraat 1 9240 Zele Belgium Tél.: (32)(0) 52/45.60.11 Fax : (32)(0) 52/45.00.34

www.crcind.com

