





Date	SYM	REVISION RECORD	AUTH	DR.	CK.
07/29/11	B	UPDATED NOTES	T.B.	B.S.	
05/17/13	C	UPDATED TITLE BLOCK DIM. 2.69 WAS 3.05	T.B.	B.S.	
05/24/13	D	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	
06/27/14	E	ADDED GROOVE ON SIDES	T.B.	B.S.	



NOTES:

MATERIAL: GLASS FILLED NYLON 66, UL94V-0
 COLOR BLACK, UL FILE NO. E196894
 CONTACTS: PHOSPHOR BRONZE, C5191, NICKEL PLATED
 ELECTRICAL :
 VOLTAGE: 250V AC
 CONTACT RESISTANCE: 30mΩ MAX
 INSULATION RESISTANCE: 1000mΩ AT DC 500V
 DIELECTRIC STRENGTH: AC 1000V PER MINUTE
 TEMPERATURE RANGE: -40°C TO +200°C
 ROHS 2 COMPLIANT

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735	Scale	Drawn By B.S.
		Approved By T.B.	
decimal ±.5 (.020)	Title BR/CR/DL 1225 VERTICAL BATTERY HOLDER, 3 PINS		
Fractional ± .8 (.030)	Date 6/27/14	Drawing Number BS-1225-PC	
Angular ± 3°			