

Product data sheet

636 084 3

Crimping machine CM 25-3

With ferrule crimping unit

- Compact, maintenance-free tabletop machine in several variants
- Hand or foot actuation
- Height-adjustable feet
- Quick and simple retooling makes it suitable for short- and medium-run production
- Crimp unit for insulated and uninsulated 0.08 mm² to 10 mm² ferrules
- Square crimp profile with 4 profiled crimp surfaces
- Self-adjusting adaptation to the required size of ferrule
- Adjustable insertion guide for insulated ferrules



General

Item number	636 084 3
EAN	4049002097348
Weight	32,400 g
Dimension	325 x 280 x 500 mm

Specifications

Crimp force	25 kN
Operating pressure	6 bar
Air requirement per working stroke	0.75 l
Range of applications	Ferrules
Capacity	0.08 – 10.0 mm ²

Contents

636 084 3 0	Ferrule Crimping Unit, Square Crimp, 0.08 — 10.0 mm ²
-------------	--

With reservations regarding technical modifications and errors. Illustration may vary.