

MB322-500M

RoHS
Compliant

CE

VDE

CULUS






□ □ : Poles

500 : Pitch 5.00mm

322 : Standard

MB : Type

PCB Layout



Pitch : 5.00mm(0.197inch)

Poles	A(mm)	A(in)	Poles	A(mm)	A(in)
2	10.00	0.394	15	75.00	2.953
3	15.00	0.591	16	80.00	3.150
4	20.00	0.787	17	85.00	3.346
5	25.00	0.984	18	90.00	3.543
6	30.00	1.181	19	95.00	3.740
7	35.00	1.378	20	100.00	3.937
8	40.00	1.575	21	105.00	4.134
9	45.00	1.772	22	110.00	4.331
10	50.00	1.969	23	115.00	4.528
11	55.00	2.165	24	120.00	4.724
12	60.00	2.362	25	125.00	4.921
13	65.00	2.559			
14	70.00	2.756			

Current rating : 16Amp AC300V

Insulation withstands volt : AC2000V min

Insulation resistance : >2000MΩ DC500V

Operation temperature : -40°C to +105°C

Wire strip length : 4mm~5mm

Wire range : 12~26 AWG

Screw torque : 5.0 lb-inch

DECA
SwitchLab

Switchlab INC.

	Material	Plating/Finish	Remark
1	Insulating body	Polyamide 66(UL94V-0)	Green
2	Cage clamp	Brass	Ni plated
3	Terminal	Brass	Tin plated
4	Screw	Steel	Ni plated