



SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

GLUE STICK 2609256D30, 2609256.D31, 2609256D32

Further trade names

Bosch:

2.609.256.D30, 2.609.256.D31, 2.609.256.D32

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of the substance/mixture

Construction adhesive

1.3. Details of the supplier of the safety data sheet

Robert Bosch GmbH

Power Tools

Max-Lang-Straße 40-46

D-70771 Leinfelden-Echterdingen

Telephone: +49 (0)711-758-0

www.bosch-pt.com

Responsible for the safety data sheet: sds@gbk-ingelheim.de

1.4. Emergency telephone number: +49 (0) 6132 / 84463 (GBK GmbH)

number:

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

This mixture is not classified as hazardous according to Directive 1999/45/EC.

Classification according to Regulation (EC) No. 1272/2008 [CLP]

This mixture is not classified as hazardous according to Regulation (EC) No. 1272/2008.

2.2. Label elements

Additional advice on labelling

The product does not require a hazard warning label in accordance with EC directives/the relevant national laws.

2.3. Other hazards

Not known.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Chemical characterization

Polymer

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Remove contaminated soaked clothing immediately.

If you feel unwell, seek medical advice.

After inhalation

Move to fresh air in case of accidental inhalation of vapours or decomposition products.

In the event of symptoms refer for medical treatment.

After contact with skin

In case of contact with the hot melt, cool with water. Seek medical attention.

After contact with eyes

In case of contact with the hot melt, cool with water. Seek medical attention.

After ingestion

Rinse out mouth and give plenty of water to drink.

Do not induce vomiting.

Consult a physician.

4.2. Most important symptoms and effects, both acute and delayed

Not known.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptoms.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Foam, carbon dioxide (CO₂), dry chemical, water-spray.

Fire-extinguishing activities according to surrounding.

Extinguishing media which must not be used for safety reasons

Full water jet.

5.2. Special hazards arising from the substance or mixture

Fire may produce:

Irritant/corrosive, flammable as well as toxic distillation gases (carbonization gases).

5.3. Advice for firefighters

Use breathing apparatus with independent air supply.

Protective suit.

Additional information

Cool containers at risk with water spray jet.

Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin, eyes and clothing.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not discharge into the drains/surface waters/ground water.

6.3. Methods and material for containment and cleaning up

Allow to solidify.

Take up mechanically and collect in suitable container for disposal.

6.4. Reference to other sections

Observe protective instructions (see Sections 7 and 8).

Information for disposal see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Avoid contact with skin, eyes and clothing.

Use only in well-ventilated areas.

Advice on protection against fire and explosion

No special protective measures against fire required.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed in a dry, cool and well-ventilated place.

Further information on storage conditions

Keep away from food, drink and animal feeding stuffs.

Storage class (D): 11

7.3. Specific end use(s)

Construction adhesive

SECTION 8: Exposure controls/personal protection

8.1. Control parameters



8.2. Exposure controls

Occupational exposure controls

Ensure adequate ventilation, especially in confined areas.

Protective and hygiene measures

Wash hands before breaks and at the end of workday.

When using do not eat, drink or smoke.

Avoid contact with skin, eyes and clothing.

Remove and wash contaminated clothes before re-use.

Respiratory protection

No personal respiratory protective equipment normally required.

Hand protection

When handling hot melt, wear heat-proof protective gloves.

Eye protection

Safety goggles with side protection (EN 166).

Skin protection

Use personal protective clothing.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Solid
Colour:	Product-specific
Odour:	resinlike

Test method

Changes in the physical state

Softening point:	82 - 90 °C
Flash point:	> 200 °C
Lower explosion limits:	n.d.
Upper explosion limits:	
Ignition temperature:	n.d.
Vapour pressure: (at 20 °C)	n.d.
Density (at 20 °C):	0,9 - 0,98 g/cm ³
Water solubility: (at 20 °C)	insoluble

9.2. Other information

No data available.

SECTION 10: Stability and reactivity

10.1. Reactivity

No decomposition if stored and applied as directed.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No hazardous reactions known.

10.4. Conditions to avoid

To avoid thermal decomposition, do not overheat.

Avoid temperatures above 300°C.

10.5. Incompatible materials

No materials to be especially mentioned.

10.6. Hazardous decomposition products

Fire may produce:

Irritant/corrosive, flammable as well as toxic distillation gases (carbonization gases).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

No toxicological data available.

Irritation and corrosivity

Skin irritation: Not classified.

Eye irritation: Not classified.

Sensitising effects

Not classified.

Severe effects after repeated or prolonged exposure

STOT - Single exposure: Not classified.

STOT - Repeated exposure: Not classified.

Aspiration hazard: Not classified.

Carcinogenic/mutagenic/toxic effects for reproduction

Carcinogenicity: Not classified.

Mutagenicity: Not classified.

Teratogenicity: Not classified.

Additional information on tests

Classification in compliance with the assessment procedure specified in the Regulation (EC) no 1272/2008.

Empirical data on effects on humans

If appropriately handled and if in accordance with the general hygienic rules, no damages to health have become known.

SECTION 12: Ecological information

12.1. Toxicity

Ecological data are not available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

According to Regulation (EC) No 1907/2006 (REACH) none of the substances, contained in this product are a PBT / vPvB substance.

12.6. Other adverse effects

No data available.

Further information

Do not flush into surface water or sanitary sewer system.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Can be incinerated, when in compliance with local regulations.

Where possible recycling is preferred to disposal.

Waste disposal number of waste from residues/unused products

080410 WASTES FROM THE MANUFACTURE, FORMULATION, SUPPLY AND USE (MFSU) OF COATINGS (PAINTS, VARNISHES AND VITREOUS ENAMELS), ADHESIVES, SEALANTS AND PRINTING INKS; wastes from MFSU of adhesives and sealants (including waterproofing products); waste adhesives and sealants other than those mentioned in 08 04 09

Contaminated packaging

Empty containers should be taken for local recycling, recovery or waste disposal.

Contaminated packaging should be emptied as far as possible and after appropriate cleansing may be taken for reuse.

Packaging that cannot be cleaned should be disposed of like the product.



SECTION 14: Transport information

Other applicable information

No hazardous material as defined by the transport regulations.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulatory information

1999/13/EC (VOC): 0 %

National regulatory information

Water contaminating class (D): 1 - slightly water contaminating

15.2. Chemical safety assessment

For this substance a chemical safety assessment has not been carried out.

SECTION 16: Other information

Abbreviations and acronyms

ADR = Accord européen relatif au transport international des marchandises Dangereuses par Route
RID = Règlement concernant le transport international ferroviaire de marchandises dangereuses
ADN = Accord européen relatif au transport international des marchandises dangereuses par voie de navigation intérieure
IMDG = International Maritime Code for Dangerous Goods
IATA/ICAO = International Air Transport Association / International Civil Aviation Organization
MARPOL = International Convention for the Prevention of Pollution from Ships
IBC = Code International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk
GHS = Globally Harmonized System of Classification and Labelling of Chemicals
REACH = Registration, Evaluation, Authorization and Restriction of Chemicals
CAS = Chemical Abstract Service
EN = European norm
ISO = International Organization for Standardization
VOC = Volatile organic compound
STOT SE = Specific target organ toxicity single exposure
STOT RE = Specific target organ toxicity repeated exposure
PBT = Persistent Bioaccumulative and Toxic
vPvB = Very Persistent and very Bio-accumulative
bw = body weight
LD = Lethal dose
LC = Lethal concentration
EC = Effect concentration
IC = Median immobilisation concentration or median inhibitory concentration

Further Information

Data of items 4 to 8, as well as 10 to 12, do partly not refer to the use and the regular employing of the product (in this sense consult information on use and on product), but to liberation of major amounts in case of accidents and irregularities.

The information describes exclusively the safety requirements for the product(s) and is based on the present level of our knowledge.

The delivery specifications are contained in the corresponding product sheet.

This data does not constitute a guarantee for the characteristics of the product(s) as defined by the legal warranty regulations.

(n.a. = not applicable; n.d. = not determined)

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)