



**Part no.: 50040820**  
**TKS 40X60**  
**Reflector**



Figure can vary

## Contents

- Technical data
- Accessories



Part no.: 50040820 – TKS 40X60 – Reflector

## Technical data

<b>Mechanical data</b>	
Design	Rectangular
Mounting dimension, width	41 mm
Reflection surface width	37 mm
Mounting dimension, height	60 mm
Reflection surface height	56 mm
Mounting dimension, thickness	8 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	14 g
Type of fastening	Adhesive Through-hole mounting
Type of reflector	Reflector



<b>Environmental data</b>	
Ambient temperature, operation	-40 ... 70 °C

<b>Certifications</b>	
Degree of protection	IP 67


<b>Classification</b>	
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467

## Accessories

### Mounting technology - Rod mounts

	Part no.	Designation	Article	Description
	50082084	BT 450.1-96	Mounting device	Design of mounting device: Mounting system Mounting bracket, at system: For 10 mm rod Mounting bracket, at device: Screw type Type of mounting device: Turning, 360°, Adjustable Material: Metal
	50119332	BTU 900M-D10	Mounting system	Contains: 2x M4 x 10 screw, 2x position washers Design of mounting device: Mounting system Mounting bracket, at system: For 10 mm rod, Sheet-metal mounting Mounting bracket, at device: Screw type Type of mounting device: Clampable, Turning, 360°, Swiveling Material: Metal
	50119331	BTU 900M-D12	Mounting system	Contains: 2x position washers, 2x M4 x 10 screw Design of mounting device: Mounting system Mounting bracket, at system: For 12 mm rod, Sheet-metal mounting Mounting bracket, at device: Screw type Type of mounting device: Clampable, Turning, 360°, Swiveling Material: Metal

Part no.: 50040820 – TKS 40X60 – Reflector

	Part no.	Designation	Article	Description
	50119330	BTU 900M-D14	Mounting system	Contains: 2x position washers, 2x M4 x 10 screw Design of mounting device: Mounting system Mounting bracket, at system: For 14 mm rod, Sheet-metal mounting Mounting bracket, at device: Screw type Type of mounting device: Clampable, Turning, 360°, Swiveling Material: Metal