

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 1 of 8

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Zinc Spray bright

1.2. Relevant identified uses of the substance or mixture and uses advised against**Uses advised against**

Reserved for industrial and professional use.

1.3. Details of the supplier of the safety data sheet

Company name: ITW LLC & Co. KG
Street: Mühlackerstrasse 147
Place: D-75417 Mühlacker
Telephone: ++49(0)7041-96340 Telefax: ++49(0)7041-963429
e-mail: info@itwcp.de
Internet: www.itwcp.de
Responsible Department: Produktsicherheit

1.4. Emergency telephone number: ++49(0)7041-96340
Mo. - Do. 8.00 - 16.30 Fr. 8.00 - 14.00

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Directive 67/548/EEC or 1999/45/EC**

Indications of danger: F+ - Extremely flammable
R phrases:
Extremely flammable.
Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
Vapours may cause drowsiness and dizziness.

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Hazard Statements:
Extremely flammable aerosol.
Pressurised container: May burst if heated.
Causes serious eye irritation.
Causes skin irritation.
May cause drowsiness or dizziness.
Harmful to aquatic life with long lasting effects.

2.2. Label elements**Hazardous components which must be listed on the label**

Acetone, Hydrocarbons, C 6 isoalkanes

Signal word: Danger
Pictograms: GHS02-GHS07

**Hazard statements**

H222 Extremely flammable aerosol.
H229 Pressurised container: May burst if heated.
H319 Causes serious eye irritation.



Safety Data Sheet

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 2 of 8

H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H412	Harmful to aquatic life with long lasting effects.

Precautionary statements

P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P271	Use only outdoors or in a well-ventilated area.
P251	Do not pierce or burn, even after use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P102	Keep out of reach of children.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Hazardous components

EC No	Chemical name	Quantity
CAS No	Classification according to Directive 67/548/EEC	
Index No	Classification according to Regulation (EC) No. 1272/2008 [CLP]	
REACH No		
203-448-7	butane	30-40%
106-97-8	F+ - Extremely flammable R12	
601-004-00-0	Flam. Gas 1; H220	
200-827-9	propane	10-30%
74-98-6	F+ - Extremely flammable R12	
601-003-00-5	Flam. Gas 1; H220	
215-535-7	xylene	5-15 %
1330-20-7	Xn - Harmful, Xi - Irritant R10-20/21-38	
601-022-00-9	Flam. Liq. 3, Acute Tox. 4, Acute Tox. 4, Skin Irrit. 2; H226 H332 H312 H315	
200-662-2	acetone; propan-2-one; propanone	10-15%
67-64-1	F - Highly flammable, Xi - Irritant R11-36-66-67	
606-001-00-8	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3; H225 H319 H336 EUH066	
265-151-9	Naphtha (petroleum), hydrotreated light; Low boiling point hydrogen treated naphtha	5-10 %
64742-49-0	F - Highly flammable, Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R11-38-51-53-65	
	Flam. Liq. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H336 H304 H411	
01-2119484651-34		
231-175-3	zinc powder - zinc dust (stabilized)	2,5-5%
7440-66-6	N - Dangerous for the environment R50-53	
030-001-01-9	Aquatic Acute 1 (M-Factor = 1), Aquatic Chronic 1 (M-Factor = 1); H400 H410	
	Solvent naphtha light	<1%
64742-95-6	Xn - Harmful, Xi - Irritant, N - Dangerous for the environment R10-37-51-53-65	
	Flam. Liq. 3, STOT SE 3, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H226 H335 H336 H304 H411	

Full text of R-, H- and EUH-phrases: see section 16.



Safety Data Sheet

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 3 of 8

SECTION 4: First aid measures

4.1. Description of first aid measures

After inhalation

Provide fresh air.

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

Rinse immediately carefully and thoroughly with eye-bath or water.

After ingestion

If swallowed, immediately drink: Water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂). Foam. Extinguishing powder.

Unsuitable extinguishing media

Water with tenside additive. Water.

5.2. Special hazards arising from the substance or mixture

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Use water spray jet to protect personnel and to cool endangered containers.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Remove all sources of ignition.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition. - No smoking.

7.2. Conditions for safe storage, including any incompatibilities

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 4 of 8

Requirements for storage rooms and vessels

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition.
- No smoking.

Advice on storage compatibility

Do not store together with: Material, rich in oxygen, oxidizing.

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Exposure limits (EH40)**

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
67-64-1	Acetone	500	1210		TWA (8 h)	WEL
		1500	3620		STEL (15 min)	WEL
106-97-8	Butane	600	1450		TWA (8 h)	WEL
		750	1810		STEL (15 min)	WEL
1330-20-7	Xylene: mixed isomers	50	220		TWA (8 h)	WEL
		100	441		STEL (15 min)	WEL

Biological Monitoring Guidance Values (EH40)

CAS No	Substance	Parameter	Value	Test material	Sampling time
1330-20-7	Xylene, o-, m-, p- or mixed isomers	methyl hippuric acid	650 mmol/mol	urine	Post shift

8.2. Exposure controls**Appropriate engineering controls**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Change contaminated clothing. Wash hands before breaks and after work. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: Butyl rubber. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state:	Aerosol
Colour:	silver grey
Odour:	Solvent/Thinner.

Test method

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 5 of 8

Changes in the physical state

Initial boiling point and boiling range:	-0,5 °C
Flash point:	< 0 °C
Lower explosion limits:	2,5 vol. %
Upper explosion limits:	14,3 vol. %
Ignition temperature:	365 °C
Vapour pressure:	246 hPa
(at 20 °C)	
Vapour pressure:	814 hPa
(at 50 °C)	
Density:	0,882 g/cm ³
Solvent content:	9,99 %

SECTION 10: Stability and reactivity**10.1. Reactivity**

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Acute toxicity**

CAS No	Chemical name	Exposure routes	Method	Dose	Species	Source
106-97-8	butane	inhalative (4 h) gas	LC50	273000 ppm	Rat	GESTIS
1330-20-7	xylene	dermal	ATE	1100 mg/kg		
		inhalative gas	ATE	4500 ppm		
67-64-1	acetone; propan-2-one; propanone	oral	LD50	5800 mg/kg	Rat	RTECS
		dermal	LD50	20000 mg/kg	Rabbit	IUCLID
		inhalative (4 h) vapour	LC50	76 mg/l	Rat	

Additional information on tests

The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).



Safety Data Sheet

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 6 of 8

SECTION 12: Ecological information

12.1. Toxicity

CAS No	Chemical name	Method	Dose	[h] [d]	Species	Source
67-64-1	acetone; propan-2-one; propanone					
	Acute fish toxicity	LC50	5540 mg/l	96 h	Onchorhynchus mykiss	
	Acute crustacea toxicity	EC50	6100 mg/l	48 h	Daphnia magna	

12.3. Bioaccumulative potential

Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
106-97-8	butane	2,89
74-98-6	propane	2,36
67-64-1	acetone; propan-2-one; propanone	-0,24

Further information

Do not allow to enter into surface water or drains. The classification was carried out according to the calculation method of the Preparations Directive (1999/45/EC).

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Advice on disposal

Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing dangerous substances
Classified as hazardous waste.

Waste disposal number of contaminated packaging


150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1. UN number:	UN1950
14.2. UN proper shipping name:	AEROSOLS
14.3. Transport hazard class(es):	2
Hazard label:	2.1
	
Classification code:	5F
Special Provisions:	190 327 625
Limited quantity:	1 L



Safety Data Sheet

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 7 of 8

Transport category: 2
Tunnel restriction code: D

Other applicable information (land transport)
E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)
E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)
E0

Air transport (ICAO)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS, flammable
14.3. Transport hazard class(es): 2.1
Hazard label: 2.1



Special Provisions: A145 A167
Limited quantity Passenger: 30 kg G
IATA-packing instructions - Passenger: 203
IATA-max. quantity - Passenger: 75 kg
IATA-packing instructions - Cargo: 203
IATA-max. quantity - Cargo: 150 kg

**Safety Data Sheet**

according to Regulation (EC) No 1907/2006

Zinc Spray bright

Print date: 01.06.2015

Product code: VB_83

Page 8 of 8

Other applicable information (air transport)E0
: Y203**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: no

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

2004/42/EC (VOC): 34,98 %

National regulatory information

Water contaminating class (D): 2 - water contaminating

SECTION 16: Other information**Relevant R-phrases (Number and full text)**

- | | |
|-------|---|
| 10 | Flammable. |
| 11 | Highly flammable. |
| 12 | Extremely flammable. |
| 20/21 | Harmful by inhalation and in contact with skin. |
| 36 | Irritating to eyes. |
| 37 | Irritating to respiratory system. |
| 38 | Irritating to skin. |
| 50 | Very toxic to aquatic organisms. |
| 51 | Toxic to aquatic organisms. |
| 53 | May cause long-term adverse effects in the aquatic environment. |
| 65 | Harmful: may cause lung damage if swallowed. |
| 66 | Repeated exposure may cause skin dryness or cracking. |
| 67 | Vapours may cause drowsiness and dizziness. |

Relevant H- and EUH-phrases (Number and full text)

- | | |
|--------|---|
| H220 | Extremely flammable gas. |
| H222 | Extremely flammable aerosol. |
| H225 | Highly flammable liquid and vapour. |
| H226 | Flammable liquid and vapour. |
| H229 | Pressurised container: May burst if heated. |
| H304 | May be fatal if swallowed and enters airways. |
| H312 | Harmful in contact with skin. |
| H315 | Causes skin irritation. |
| H319 | Causes serious eye irritation. |
| H332 | Harmful if inhaled. |
| H335 | May cause respiratory irritation. |
| H336 | May cause drowsiness or dizziness. |
| H400 | Very toxic to aquatic life. |
| H410 | Very toxic to aquatic life with long lasting effects. |
| H411 | Toxic to aquatic life with long lasting effects. |
| H412 | Harmful to aquatic life with long lasting effects. |
| EUH066 | Repeated exposure may cause skin dryness or cracking. |

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)